

C4AE, Film, Metallized Polypropylene, DC Link, 2.7 uF, 5%, 900 VDC, 70C, Lead Spacing = 27.5mm



General Information	
Supplier:	KEMET
Series:	C4AE
Dielectric:	Metallized Polypropylene
Style:	Radial
RoHS:	Yes
Termination:	Tin
Lead:	Wire Leads
Miscellaneous:	Thermal Resistance = 36 C/W

Dimensions	
L	31.5mm +0.5mm
H	25mm +0.2mm
T	13mm +0.3mm
S	27.5mm +/-0.4mm
LL	6mm -2mm
F	0.8mm NOM
G	0.5mm NOM

Specifications	
Capacitance:	2.7 uF
Capacitance Tolerance:	5%
Voltage DC:	900 VDC
Temperature Range:	-40/+85C
Rated Temperature:	70C
Max dV/dt:	24 V/us
Resistance:	15.3 mOhms (10kHz 70C)
Ripple Current:	5 Amps (10kHz 70C), 65 Amps (Peak)
Inductance:	25 nH

Packaging Specifications	
Packaging:	Bulk, Box