

CBR-SMD RF COG, Ceramic, High Q, 2.7 pF, +/-0.1 pF, 250 VDC, COG, SMD, Fixed, RF, Ultra High Q, Low ESR, Class I, 0603



**Dimensions**

|          |                 |
|----------|-----------------|
| <b>L</b> | 1.6mm +/-0.1mm  |
| <b>W</b> | 0.8mm +/-0.1mm  |
| <b>T</b> | 0.8mm +/-0.07mm |
| <b>B</b> | 0.4mm +/-0.15mm |

**Packaging Specifications**

|                            |                          |
|----------------------------|--------------------------|
| <b>Packaging:</b>          | T&R, 180mm, Plastic Tape |
| <b>Packaging Quantity:</b> | 4000                     |

**General Information**

|                       |  |
|-----------------------|--|
| <b>Supplier:</b>      | KEMET  |
| <b>Series:</b>        | CBR-SMD RF COG                                 |
| <b>Style:</b>         | SMD Chip                                       |
| <b>Description:</b>   | SMD, Fixed, RF, Ultra High Q, Low ESR, Class I |
| <b>Features:</b>      | Ultra High Q, Low ESR, Class I                 |
| <b>RoHS:</b>          | Yes  |
| <b>Termination:</b>   | Tin  |
| <b>Marking:</b>       | No   |
| <b>Miscellaneous:</b> | Minimum Q = 854                                |
| <b>Notes:</b>         | Solder Wave or Solder Reflow                   |
| <b>Chip Size:</b>     | 0603   |

**Specifications**

|   |                     |
|---|---------------------|
| <b>Capacitance:</b>                     | 2.7 pF              |
| <b>Capacitance Tolerance:</b>           | +/-0.1 pF           |
| <b>Voltage DC:</b>                      | 250 VDC             |
| <b>Dielectric Withstanding Voltage:</b> | 500 V               |
| <b>Temperature Range:</b>               | -55/+125C           |
| <b>Temperature Coefficient:</b>         | COG                 |
| <b>Dissipation Factor:</b>              | 0.22%               |
| <b>Aging Rate:</b>                      | 0% Loss/Decade Hour |
| <b>Insulation Resistance:</b>           | 10 GOhms            |
| <b>Quality Factor:</b>                  | 854                 |