

R75, Film, Metallized Polypropylene, General Purpose, 2.2 uF, 10%, 1000 VDC, 85C, Lead Spacing = 37.5mm



Dimensions

L	41.5mm +0.3mm
H	40mm +0.1mm
T	20mm +0.3mm
S	37.5mm +/-0.4mm
LL	25mm +2/-1mm
F	1mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	84

General Information

Supplier:	KEMET
Series:	R75
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads

Specifications

Capacitance:	2.2 uF
Capacitance Tolerance:	10%
Voltage AC:	250 VAC
Voltage DC:	1000 VDC
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	0.06% 1kHz
Insulation Resistance:	66 GOhms
Max dV/dt:	150 V/us
Inductance:	20 nH