

CBR-SMD RF COG, Ceramic, High Q, 4.7 pF, +/-0.05 pF, 50 VDC, COG, SMD, Fixed, RF, Ultra High Q, Low ESR, Class I, 0402



| Dimensions | |
|------------|---------------------|
| L | 1mm +/-0.05mm |
| W | 0.5mm +/-0.05mm |
| T | 0.5mm +/-0.05mm |
| B | 0.25mm +0.05/-0.1mm |

| Packaging Specifications | |
|--------------------------|--------------------------|
| Packaging: | T&R, 180mm, Plastic Tape |
| Packaging Quantity: | 10000 |

| General Information | |
|---------------------|--|
| Supplier: | KEMET |
| Series: | CBR-SMD RF COG |
| Style: | SMD Chip |
| Description: | SMD, Fixed, RF, Ultra High Q, Low ESR, Class I |
| Features: | Ultra High Q, Low ESR, Class I |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| Miscellaneous: | Minimum Q = 894 |
| Notes: | Solder Reflow Only |
| Chip Size: | 0402 |

| Specifications | |
|----------------------------------|---------------------|
| Capacitance: | 4.7 pF |
| Capacitance Tolerance: | +/-0.05 pF |
| Voltage DC: | 50 VDC |
| Dielectric Withstanding Voltage: | 125 V |
| Temperature Range: | -55/+125C |
| Temperature Coefficient: | COG |
| Dissipation Factor: | 0.20% |
| Aging Rate: | 0% Loss/Decade Hour |
| Insulation Resistance: | 10 GOhms |
| Quality Factor: | 894 |