


KEMET, EE2, Relays, Signal



Dimensions

| Dimension | Value |
|-----------|-----------------|
| L | 15mm MAX |
| W | 7.5mm MAX |
| H | 10.35mm MAX |
| LL | 1.35mm +/-0.2mm |
| S | 5.08mm +/-0.2mm |
| S1 | 2.54mm +/-0.2mm |
| F | 1mm +/-0.2mm |
| F1 | 2.73mm +/-0.1mm |

Packaging Specifications

| | |
|-------------------|-----|
| Packaging: | T&R |
|-------------------|-----|

General Information

| | |
|---------------------|---|
| Series: | EE2 |
| Style: | SMD |
| Description: | Miniature Signal Relay, Single Coil Latch |
| Features: | Compact and light weight. FCC (1500 V) and Telcordia (2500 V) surge capacity. UL recognized and CSA certified. Low power consumption (100-200 mW). ND type (High insulation). NKX type (High breakdown voltage) can withstand 1.5KVAC at open contacts. |
| RoHS: | Yes |
| Coil Type: | Single Coil (Latching) |

Specifications

| | |
|---------------------------------|--------------------------------------|
| Temperature Range: | -40/+85C |
| Coil Voltage: | 5 V |
| Coil Resistance: | 250 Ohms +/-10% |
| Contact Form: | 2 Form C (DPDT) |
| Contact Material: | Silver Alloy With Gold Alloy Overlay |
| Voltage Characteristics: | 3.75 (Set/Reset) |
| Switching Power: | 60 W, 125 VA |
| Switching Voltage DC: | 220 V |
| Switching Voltage AC: | 250 VAC |
| Switching Current: | 2 A |
| Contact Current Class: | >10A |
| Carrying Current: | 2 Amps |
| Contact Resistance: | 75 mOhms |
| Operation Time: | Approximately 2ms |
| Release Time: | Approximately 1ms |
| Insulation Resistance: | 1 GOhms |
| Withstanding Voltage: | 1000 VAC (1min) 1500 V Surge |