


C44A, Film, Metallized Polypropylene, Power, 100 uF, 5%, 400 VAC, 700 VDC



Threaded Mounting Stud  
 D < 55: M8x10  
 D >= 55: M12x12,5

**Dimensions**

<b>D</b>	85mm +/-0.5mm
<b>L</b>	185mm +/-2mm
<b>S</b>	35mm +/-0.5mm

**Packaging Specifications**

<b>Mounting:</b>	Bolt - M12x12.5
<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	5

**General Information**

<b>Supplier:</b>	KEMET
<b>Series:</b>	C44A
<b>Dielectric:</b>	Metallized Polypropylene
<b>Style:</b>	Can
<b>RoHS:</b>	Yes
<b>Lead:</b>	Threaded Studs M10
<b>Miscellaneous:</b>	Thermal Resistance = 2 C/W

**Specifications**

<b>Capacitance:</b>	100 uF
<b>Capacitance Tolerance:</b>	5%
<b>Voltage AC:</b>	400 VAC
<b>Voltage DC:</b>	700 VDC
<b>Temperature Range:</b>	-40/+85C
<b>Rated Temperature:</b>	70C
<b>Max dV/dt:</b>	40 V/us
<b>Resistance:</b>	3 mOhms (TYP)
<b>Ripple Current:</b>	50 Amps, 4000 Amps (Peak)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.