

C4AT, Film, Metallized Polypropylene, Power, 3.3 uF, 5%, 275 VAC, 450 VDC, 70C, Lead Spacing = 27.5mm



Dimensions

L	32mm NOM
H	33mm NOM
T	18mm NOM
S	27.5mm +/-0.4mm
LL	6mm -2mm
F	1.2mm NOM

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	80

General Information

Supplier:	KEMET
Series:	C4AT
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	Switching
RoHS:	Yes
Lead:	Wire Leads

Specifications

Capacitance:	3.3 uF
Capacitance Tolerance:	5%
Voltage AC:	275 VAC
Voltage DC:	450 VDC
Temperature Range:	-40/+85C
Rated Temperature:	70C
Dissipation Factor:	0.05%
Max dV/dt:	82 V/us
Resistance:	3.8 mOhms (100kHz)
Ripple Current:	14 Amps (100kHz 70C), 269 Amps (Peak)