

R46\_310, Film, Metallized Polypropylene, Safety, 0.022 uF, 10%, 310 VAC (X2), 630 VDC, 110C, Lead Spacing = 10mm



#### Dimensions

Parameter	Value
L	13mm +0.2mm
H	9mm +0.1mm
T	4mm +0.2mm
S	10mm +/-0.4mm
LL	4mm +2mm
F	0.6mm +/-0.05mm

#### Packaging Specifications

<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	2000

#### General Information

<b>Supplier:</b>	KEMET
<b>Series:</b>	R46_310
<b>Dielectric:</b>	Metallized Polypropylene
<b>Style:</b>	Radial
<b>Features:</b>	EMI Safety
<b>RoHS:</b>	Yes
<b>Lead:</b>	Cut
<b>Qualifications:</b>	ENEC, UL, cUL, CQC

#### Specifications

<b>Capacitance:</b>	0.022 uF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage AC:</b>	310 VAC (X2)
<b>Voltage DC:</b>	630 VDC
<b>Temperature Range:</b>	-40/+110C
<b>Rated Temperature:</b>	110C
<b>Dissipation Factor:</b>	0.10% 1kHz
<b>Insulation Resistance:</b>	100 GOhms
<b>Max dV/dt:</b>	500 V/us
<b>Safety Class:</b>	X2