

KEMET Part Number: PME264NC5220MR30
(P264CJ223M660A)

PME264/P264, Film, Metallized Paper, Safety, 0.022 uF, 20%, 660 VAC (X2), 1500 VDC, 85C, Lead Spacing = 20.3mm



| General Information | |
|---------------------|------------------|
| Supplier: | KEMET |
| Series: | PME264/P264 |
| Dielectric: | Metallized Paper |
| Style: | Radial |
| Features: | EMI Safety |
| RoHS: | Yes |
| Lead: | Wire Leads |
| Qualifications: | ENEC, UL, cUL |
| Construction: | Molded |

| Dimensions | |
|------------|-----------------|
| L | 24mm MAX |
| H | 15mm MAX |
| T | 9mm MAX |
| S | 20.3mm +/-0.5mm |
| LL | 30mm +5mm |
| F | 0.8mm NOM |

| Specifications | |
|------------------------|--------------|
| Capacitance: | 0.022 uF |
| Capacitance Tolerance: | 20% |
| Voltage AC: | 660 VAC (X2) |
| Voltage DC: | 1500 VDC |
| Temperature Range: | -40/+85C |
| Rated Temperature: | 85C |
| Dissipation Factor: | 1.3% 1kHz |
| Insulation Resistance: | 12 GOhms |
| Max dV/dt: | 1400 V/us |
| Safety Class: | X2 |

| Packaging Specifications | |
|--------------------------|-----------|
| Packaging: | Bulk, Bag |
| Packaging Quantity: | 200 |