

KEMET Part Number: PME264NB4470MR30
(P264QE472M660A)

PME264/P264, Film, Metallized Paper, Safety, 4700 pF, 20%, 660 VAC (X2), 1500 VDC, 85C, Lead Spacing = 15.2mm



General Information	
Supplier:	KEMET
Series:	PME264/P264
Dielectric:	Metallized Paper
Style:	Radial
Features:	EMI Safety
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	ENEC, UL, cUL
Construction:	Molded

Dimensions	
L	18.5mm MAX
H	10.5mm MAX
T	5.2mm MAX
S	15.2mm +/-0.5mm
LL	30mm +5mm
F	0.8mm NOM

Specifications	
Capacitance:	4700 pF
Capacitance Tolerance:	20%
Voltage AC:	660 VAC (X2)
Voltage DC:	1500 VDC
Temperature Range:	-40/+85C
Rated Temperature:	85C
Dissipation Factor:	1.3% 1kHz
Insulation Resistance:	12 GOhms
Max dV/dt:	2000 V/us
Safety Class:	X2

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	500