

R49, Film, Metallized Polypropylene, Safety, 0.68 uF, 10%, 330 VAC (X1), 800 VDC, 110C, Lead Spacing = 27.5mm



Dimensions

L	32mm +0.3mm
H	22mm +0.1mm
T	13mm +0.2mm
S	27.5mm +/-0.4mm
LL	4mm +2mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	480

General Information

Supplier:	KEMET
Series:	R49
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	EMI Safety
RoHS:	Yes
Lead:	Cut
Qualifications:	ENEC, UL, cUL

Specifications

Capacitance:	0.68 uF
Capacitance Tolerance:	10%
Voltage AC:	330 VAC (X1)
Voltage DC:	800 VDC
Temperature Range:	-40/+110C
Rated Temperature:	110C
Dissipation Factor:	0.10% 1kHz
Insulation Resistance:	44.1176 GOhms
Max dV/dt:	200 V/us
Safety Class:	X1