

# XLR-51 Supercapacitor

## 51 V, 188 F Rugged Module



### Description

Eaton supercapacitors are high reliability, high power, ultra-high capacitance energy storage devices utilizing electrochemical double layer capacitor (EDLC) construction combined with proprietary materials and processes. This combination of advanced technologies allows Eaton to offer a wide variety of capacitor solutions tailored to applications for back up power, pulse power and hybrid power systems. They can be applied as the sole energy storage or in combination with batteries to optimize cost, life time and run time. System requirements can range from a few micro-amps to megawatts. All products feature low ESR for high power density with environmentally friendly materials for a green power solution. Eaton supercapacitors are maintenance-free with design lifetimes up to 20 years.

### Features

- Ultra low ESR provides high efficiency, high power
- Industry standard form factor for easy integration
- High power density to optimize system size and low operating costs
- Millions of charge/discharge cycles for life of application
- No heavy metals, RoHS compliant, non-hazardous energy storage
- Heavy duty metal housing for high vibration, high current applications
- IP65 environmental rating for high dust areas and water jet washable

### Applications

- Hybrid and electric vehicles
- Grid storage
- Commercial vehicles: trucks, mining, construction
- Automated guided vehicle (AGV)
- Trolley, subway
- Marine



Powering Business Worldwide

## Ratings

|                             |  |
|-----------------------------|--|
| Capacitance                 | 188 F  |
| Maximum working voltage     | 51.3 V   |
| Surge voltage               | 54.0 V   |
| Capacitance tolerance       | 0% to +20% (+20 °C)  |
| Operating temperature range | -40 °C to +65 °C   |
| Extended temperature range  | -40 °C to +85 °C (with linear derating to 41.0 V @ +85 °C) |

## Specifications

| Capacitance (F) | Part Number   | Maximum initial ESR <sup>1</sup> (mΩ) | Nominal leakage current <sup>2</sup> (mA) | Stored energy <sup>3</sup> (Wh) | Peak power <sup>4</sup> (kW) | Pulse current <sup>5</sup> (A) | Continuous current <sup>6</sup> (A) | Typical thermal resistance <sup>7</sup> Rth (°C/W) | Short circuit current <sup>8</sup> (A) |
|-----------------|---------------|---------------------------------------|---|---------------------------------|------------------------------|--------------------------------|-------------------------------------|--|--|
| 188             | XLR-51R3187-R | 5.0                                   | 8.0                                       | 68.7                            | 131.6                        | 2485                           | 86                                  | 0.4  | 10200                                  |

## Performance

| Parameter (F)                                | Capacitance change (% of initial value) | ESR (% of maximum initial value) |
|--|---|----------------------------------|
| Life (1500 hours @ +65 °C/51.3 Vdc)          | ≤ 20%                                   | ≤ 200%                           |
| Storage – 3 years (uncharged, +30 °C)        | ≤ 5%                                    | ≤ 10%                            |
| Cycling life <sup>9</sup> (1,000,000 cycles) | ≤ 20%                                   | ≤ 200%                           |

1. Capacitance, Equivalent Series Resistance (ESR) measured according to IEC62391-1 at +20 °C, with current in milliamps (mA) = 8°C\*V

2. Leakage current at +20 °C after 72 hour charge and hold.

3. Energy (Wh) =  $\frac{0.5 \times C \times V^2}{3600} \times 1000$

4. Peak Power (W) =  $\frac{V^2}{4 \times \text{ESR}}$

5. Pulse current in Amps (A), 1 second discharge from maximum working voltage to half rated voltage. =  $\frac{0.5 \times V \times C}{(1 + \text{ESR} \times C)}$

6. Continuous current with a 15 °C temperature rise. Continuous current (A) =  $\sqrt{\frac{P}{\text{ESR} \times R_{th}}}$

7. Thermal resistance (Rth) cell body temperature to ambient in open air in degrees C per Watt (°C/W).

8. Short circuit current is for safety information only. Do not use as operating current.


9. Cycling between maximum working voltage and half voltage with 3 seconds rest at +25 °C.

## Standards and certifications

|                     |  |
|---------------------|--|
| Shock and vibration | IEC 61373 Cat. 1, Class B, SAE J2380, IEC16750-3 Table 14, SAE J2464 |
| Warnings            | Do not overvoltage, do not reverse polarity.                         |
| Environmental       | IP65, RoHS   |
| Shipping            | UN3499, <10 Wh, Non-hazardous when shipped with shorting wire.       |

**Dimensions (mm) and Mass (kg)**

| Part Number   | W (max) | L (max) | H (max) | Typical Mass (kg) |
|---------------|---------|---------|---------|-------------------|
| XLR-51R3187-R | 177     | 421     | 196     | 14.7              |



**Part numbering system**

| XLM               | — 51R3                    | 18   | 7          | -R               |
|-------------------|---------------------------|--|------------|------------------|
| Family Code       | Voltage (V)<br>R= decimal | Capacitance (µF)                             |            |                  |
|                   |                           | Value  | Multiplier |                  |
| XLR = Family code | 51R3= 51.3 V              | Example 188=18 x 10 <sup>7</sup> µF or 188 F |            | Standard product |

**Packaging information**

- Standard packaging: 1 piece per box

**Part marking**

- Manufacturer
- Capacitance (F)
- Maximum operating voltage (V)
- Part number
- Polarity
- Serial number

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

**Eaton**  
**Electronics Division**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
www.eaton.com/electronics

© 2019 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. 10765 BU-MC19011  
January 2019

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

