## Max. 20 m<sup>3</sup>/h

## DC axial fans

## □ 50 x 15 mm



Housing: GRP1) (PBT) Material: Impeller: GRP1) (PA)

Direction of air flow: Exhaust over struts **Direction of rotation:** Counterclockwise,

looking towards rotor Via single wires AWG 28,

TR 64

**Highlights:** Some models are suitable

for use at high ambient

temperatures

Weight: 27 g

1) Fiberglass-reinforced plastic


**Connection:** 

## - Possible special versions:

(See chapter DC fans - specials)

- Speed signal
- Go / NoGo alarm
- PWM control input
- Moisture protection

Series 500 F			voltage	ge	sure level	er level	re bearings Is	umption	pee	e range	L <sub>10</sub> (20 °C) standard L <sub>10</sub> (60 °C) standard	ncy L <sub>10IPC</sub> age 17	
Nominal data	Air flow	Air flow	Nominal vo	Voltage range	Sound pressure level	Sound power	Sintec sleeve I Ball bearings	Power consumption	Nominal speed	Temperature range	Service life L. ebm-papst st Service life L. ebm-papst st	Life expectancy L (40 °C) see page 1	Curve
Туре	m³/h	cfm	VDC	VDC	dB(A)	Bel(A)	■/■	Watts	rpm⁻¹	°C	Hours	Hours	
512 F	20	11.8	12	10.813.2	30	4.5		0.8	5 000	-20+70	50 000 / 20 000	52 500	2
514 F	20	11.8	24	21.626.4	30	4.5		0.9	5 000	-20+70	50 000 / 20 000	52 500	2
Model with temperature range up to +85 °C.													
512 FL-547	11	6.5	12	10.213.8	18	3.7		0.4	3 000	-20+85	50 000 / 20 000	52 500	1
512 F-532	20	11.8	12	10.813.2	30	4.5		0.9	5 000	-20+85	50 000 / 20 000	52 500	2
Subject to change													



Air performance measured according to: ISO 5801. Installation category A, without contact protection. Noise: Total sound power level  $L_WA$  ISO 103002 measured on a hemisphere with a radius of 2 m. Sound pressure level LpA measured at 1 m distance

from fan axis.

The values given are applicable only under the specified measuring conditions and may differ depending on the

installation conditions.

In the event of deviation from the standard configuration, the parameters must be checked after installation! For detailed information see http://www.ebmpapst.com/general conditions

