


**SAK Series**  
**ASK1EN/SMT 10-60VUC BFI H+**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Product image**



Similar to illustration

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Available until	2016-01-01
Type	ASK1EN/SMT 10-60VUC BFI H+
Order No.	<a href="#">9123140001</a>
Version	SAK Series, Fuse terminal, Rated cross-section: 4 mm <sup>2</sup> , Screw connection
GTIN (EAN)	4032248730919
Qty.	100 Stück
Alternative product	<a href="#">9908510001</a>

## SAK Series ASK1EN/SMT 10-60VUC BFI H+

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Width	8.1 mm	Width (inches)	0.319 inch
Height	58 mm	Height (inches)	2.283 inch
Depth	43 mm	Depth (inches)	1.693 inch
Net weight	13.71 g		

### Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

### Material data

Material	PA 66	UL 94 flammability rating	V-2
----------	-------	---------------------------	-----

### System specifications

Version	Screw connection, Fuse cartridge, One end without connector	Number of levels	1
No. of clamping points per level	2	Levels cross-connected internally	No
PE connection	No	Rail	TS 35, TS 32

### Additional technical data

Type of mounting	Snap-on
------------------	---------

### Conductors for clamping (rated connection)

Number of connections	2	Type of connection	Screw connection
-----------------------	---	--------------------	------------------

### Rating data

Rated cross-section	4 mm <sup>2</sup>	Rated voltage	60 V
Volume resistance according to IEC 60947-7-x	1 mΩ		

### Classifications

ETIM 3.0	EC000899	ETIM 4.0	EC000899
ETIM 5.0	EC000899	ETIM 6.0	EC000899
eClass 6.2	27-14-11-16	eClass 7.1	27-14-11-16
eClass 8.1	27-14-11-16	eClass 9.0	27-14-11-16
eClass 9.1	27-14-11-16		

### Approvals

Approvals	
-----------	---

ROHS	Conform
------	---------

### Safety note

Safety notice	<a href="#">Safety Information</a>
---------------	------------------------------------