

PS12_LCMS_0000_O209E_XX.X_M0

Description

12 pigtail set, LC-HQ BTW, MM, fiber colour EN / IEC, OM2



Features	Features
- High mechanical stability	
- Colour coded boot for good visibility also in mated condition	

Technical Data

General Data

Description	Values
General Typ	LC pigtail
Operation temperature	-40 up to 85°C
UL Rating	UL 94 V-0
RoHS compliant 2001/65/EU	Yes
REACH compliant	Yes


Connector left

Description	Values
Connector typ	LC pigtail
Polish	UPC
Color Housing	Black
Color Boot	Beige
Design connector acc. To	IEC 61754-20, TIA 604-10-A
Performance class H+S	0
Return Loss	>35dB
Durability	1000

Cable

Description	Values
Cable typ	Semi-tight Tube
Fiber count	1
Fiber	1 x 0.9 mm
Fiber typ	G50/125-OM2 G.651

Technical Drawing



Ordering information

Meter (m)	Item number	Description
-----------	-------------	-------------

