

Section 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

Product name: RX771C ALL COLOURS

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC1: Adhesives, sealants.

1.3. Details of the supplier of the safety data sheet

Company name: Robnor ResinLab Ltd

31 Athena Avenue

Elgin Industrial Estate

Swindon

Wiltshire

SN2 8EJ

United Kingdom

Tel: +44(0) 1793 823741

Fax: +44(0) 1793 827033

Email: eusds@robnor.co.uk**1.4. Emergency telephone number**

Emergency tel: +44(0) 1793 823741

(office hours only)

Section 2: Hazards identification**2.1. Classification of the substance or mixture**

Classification under CLP: Skin Irrit. 2: H315; Eye Irrit. 2: H319; Skin Sens. 1A: H317; Aquatic Chronic 2: H411

Most important adverse effects: Causes skin irritation. Causes serious eye irritation. May cause an allergic skin reaction.

Toxic to aquatic life with long lasting effects.

2.2. Label elements

Label elements:

Hazard statements: H315: Causes skin irritation.

H319: Causes serious eye irritation.

H317: May cause an allergic skin reaction.

H411: Toxic to aquatic life with long lasting effects.

Hazard pictograms: GHS07: Exclamation mark

GHS09: Environmental

SAFETY DATA SHEET

RX771C ALL COLOURS

Page: 2



Signal words: Warning

Precautionary statements: P280: Wear protective gloves/protective clothing/eye protection/face protection.
P261: Avoid breathing mist.
P302+P352: IF ON SKIN: Wash with plenty of water.
P332+P313: If skin irritation occurs: Get medical advice/attention.
P305+P351+P338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337+P313: If eye irritation persists: Get medical advice/attention.
P273: Avoid release to the environment.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

BISPHENOL A EPOXY RESIN (MW <700) - REACH registered number(s): 01-2119456619-26-XXXX

EINECS	CAS	PBT / WEL	CLP Classification	Percent
500-033-5	25068-38-6	-	Skin Irrit. 2: H315; Eye Irrit. 2: H319; Skin Sens. 1: H317; Aquatic Chronic 2: H411	70-90%

2-ETHYLHEXYL GLYCIDYL ETHER

219-553-6	2461-15-6	-	Skin Irrit. 2: H315; Skin Sens. 1A: H317	10-30%
-----------	-----------	---	--	--------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Drench the affected skin with running water for 10 minutes or longer if substance is still on skin.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact. May cause sensitisation in susceptible individuals.

Eye contact: There may be irritation and redness. The eyes may water profusely.

[cont...]

SAFETY DATA SHEET

RX771C ALL COLOURS

Page: 3

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Delayed effects can be expected after long-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. Mark out the contaminated area with signs and prevent access to unauthorised personnel.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed.

Suitable packaging: Must only be kept in original packaging.

[cont...]

SAFETY DATA SHEET

RX771C ALL COLOURS

Page: 4

7.3. Specific end use(s)

Specific end use(s): PC1: Adhesives, sealants.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

DNEL/PNEC Values

Hazardous ingredients:

BISPHENOL A EPOXY RESIN (MW <700)

Type	Exposure	Value	Population	Effect
DNEL	Inhalation	12.25 mg/m ³	Workers	Systemic
DNEL	Dermal	8.33 mg/kg	Workers	Systemic
PNEC	Fresh water	6 ug/L	-	-
PNEC	Marine water	600 ng/L	-	-
PNEC	Microorganisms in sewage treatment	10 mg/L	-	-
PNEC	Fresh water sediments	996 ug/kg	-	-
PNEC	Marine sediments	99.6 ug/kg	-	-
PNEC	Soil (agricultural)	196 ug/kg	-	-
PNEC	Food chain	11 mg/kg	-	-

2-ETHYLHEXYL GLYCIDYL ETHER

Type	Exposure	Value	Population	Effect
DNEL	Dermal	1 mg/kg	Workers	Systemic
DNEL	Dermal	4.17 mg/kg	Workers	Local
PNEC	Fresh water	7.2 ug/L	-	-
PNEC	Marine water	720 ng/L	-	-
PNEC	Microorganisms in sewage treatment	17 ug/L	-	-
PNEC	Fresh water sediments	286.66 mg/kg	-	-
PNEC	Marine sediments	28.66 mg/kg	-	-
PNEC	Soil (agricultural)	57.16 mg/kg	-	-

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

[cont...]

SAFETY DATA SHEET

RX771C ALL COLOURS

Page: 5

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Odour: Odourless

Viscosity: Viscous

Relative density: 1.13

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids. Amines.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

BISPHENOL A EPOXY RESIN (MW <700)

DERMAL	RAT	LD50	>2000	mg/kg
ORAL	RAT	LD50	>2000	mg/kg

2-ETHYLHEXYL GLYCIDYL ETHER

DERMAL	RAT	LD50	>2000	mg/kg
ORAL	RAT	LD50	>5000	mg/kg

[cont...]

SAFETY DATA SHEET

RX771C ALL COLOURS

Page: 6

VAPOURS	RAT	4H LC50	152	mg/l
---------	-----	---------	-----	------

Relevant hazards for product:

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
Respiratory/skin sensitisation	-	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact. May cause sensitisation in susceptible individuals.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Delayed effects can be expected after long-term exposure.

Section 12: Ecological information

12.1. Toxicity

Hazardous ingredients:

BISPHENOL A EPOXY RESIN (MW <700)

Daphnia magna	48H EC50	1.7	mg/l
GREEN ALGA (Selenastrum capricornutum)	72H ErC50	2.4	mg/l
RAINBOW TROUT (Oncorhynchus mykiss)	96H LC50	1.2	mg/l

2-ETHYLHEXYL GLYCIDYL ETHER

DAPHNIA	48H EC50	7.2	mg/l
FISH	96H LC50	>5000	mg/l

12.2. Persistence and degradability

Persistence and degradability: Not readily biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

[cont...]

SAFETY DATA SHEET

RX771C ALL COLOURS

Page: 7

12.6. Other adverse effects

Other adverse effects: Very toxic to aquatic organisms.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Waste code number: 07 02 08

Disposal of packaging: Arrange for collection by specialised disposal company.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN3082

14.2. UN proper shipping name

Shipping name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.
(BISPHENOL A EPOXY RESIN (MW <700))

14.3. Transport hazard class(es)

Transport class: 9

14.4. Packing group

Packing group: III

14.5. Environmental hazards

Environmentally hazardous: Yes

Marine pollutant: Yes

14.6. Special precautions for user

Special precautions: No special precautions.

Tunnel code: E

Transport category: 3

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

[cont...]

SAFETY DATA SHEET

RX771C ALL COLOURS

Page: 8

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H411: Toxic to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.