


T356, Tantalum, MnO<sub>2</sub> Tantalum, Commercial Grade, 10 uF, 10%, 35 VDC, Radial, Solid Tantalum, Conformal, Dipped, Lead Spacing = 5.08mm



### General Information

<b>Supplier:</b>	KEMET
<b>Series:</b>	T356
<b>Dielectric:</b>	MnO <sub>2</sub> Tantalum
<b>Style:</b>	Radial
<b>Description:</b>	Radial, Solid Tantalum, Conformal, Dipped
<b>Features:</b>	Low Leakage, Reverse Voltage
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin
<b>Notes:</b>	Longest Lead Is Positive

### Dimensions

<b>D</b>	6.3mm
<b>H</b>	11.4mm
<b>S</b>	5.08mm +/-0.38mm
<b>LL</b>	4.75mm +/-0.81mm
<b>F</b>	0.5mm +/-0.05mm

### Specifications

<b>Capacitance:</b>	10 uF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	35 VDC (85C), 23 VDC (125C), 0.35 VDC (125C Reverse)
<b>Temperature Range:</b>	-55/+125C
<b>Dissipation Factor:</b>	6.00%
<b>Leakage Current:</b>	2.8 uA

### Packaging Specifications

<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	500