# Intrinsically safe certified accelerometer



## 786A-IS

#### **SPECIFICATIONS**

Sensitivity, ±5%, 25°C	100 mV/g	
Acceleration range	80 g peak	
Amplitude nonlinearity	1%	
Frequency response: ±5%	3 - 5,000 Hz	
±10%	1 - 9,000 Hz	
±3 dB	0.5 - 14,000 Hz	
Resonance frequency	30 kHz	
Transverse sensitivity, max	5% of axial	
Temperature response: -55°C	-20%	
+120°C	+10%	
Power requirement: Voltage source	18 - 28 VDC	
Current regulating diode	2 - 10 mA	
Electrical noise, equiv. g:		
Broadband 2.5 Hz to 25 kHz	700 μg	
Spectral 10 Hz	10 μg/√Hz	
100 Hz	5 μg/√Hz	
1,000 Hz	5 μg/√Hz	
Output impedance, max	100 Ω	
Bias output voltage	12 VDC	
Grounding	case isolated, internally shielded	
Temperature range	–55° to +120°C	
Vibration limit	500 g peak	
Shock limit	5,000 g peak	
Electromagnetic sensitivity, equiv. g, max	70 μg/gauss	
Sealing	hermetic	
Base strain sensitivity, max	0.0002 g/µstrain	
Sensing element design	PZT ceramic / shear	
Weight	90 grams	
Case material	316L stainless steel	
Mounting	1/4-28 UNF tapped hole	
Output connector	2 pin, MIL-C-5015 style	
Mating connector	R6 type	

Accessories supplied: SF6 mounting stud; calibration data (level 2) Optional accessories available: ISBS-STD-08: MTL 7728 + safety barrier

#### Certifications



Class I, Div 1 Groups A, B, C, D Class II, Div 1 Groups E, F, G Class III


Class I Zone 0 AEx/Ex ia IIC T4 Ta = -50°C to 120°C



II 1 G Ex ia IIC T4 Ga Ta = -50°C to 120°C










### **Key features**

- · Hazardous area certified intrinsically safe
- MTBF 25 years
- API 670 compliant
- · Manufactured in ISO 9001 facility



Connections		
Function	Connector pin	Cable conductor color
power/signal	Α	white
common	В	black
ground	shell	shield

Note: Due to continuous process improvement, specifications are subject to change without notice. This document is cleared for public release.