

This document was generated on 03/15/2019

# PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0430451827

Status: Active

Overview: Micro-Fit 3.0 Connector System Product Family

Description: Micro-Fit 3.0 Vertical Header, 3.00mm Pitch, Dual Row, 18 Circuits, with PCB

Polarizing Peg, Tin, Glow-Wire Capable, Black

### **Documents:**

<u>Drawing (PDF)</u>
<u>3D Model</u>

Product Specification TS-46235-001-001 (PDF)

Packaging Specification PK-70873-0314-001 (PDF)

Product Specification PS-43045 (PDF)
Product Specification PS-43045-001 (PDF)
RoHS Certificate of Compliance (PDF)

Product Specification TS-43045-001-001 (PDF) Product Literature (PDF)

## **Agency Certification**

CSA LR1 UL E29

#### General


Product Family Series Application Comments LR19980 E29179

**PCB Headers** 

43045

Power, Wire-to-Board

""""This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.""""", """""This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.""""""



# **EU ELV**

Compliant

EU RoHS China RoHS

**Compliant** 

**REACH SVHC** 

Not Contained Per -ED/88/2018 (15 January 2019)

Halogen-Free

**Status** 

Low-Halogen

For more information, please visit Contact US

China ROHS Green Image
ELV Compliant
ROHS Phthalates Not Contained

# Search Parts in this Series

43045 Series

## **Mates With**

Micro-Fit 3.0 Receptacle Housing <u>43025</u> <br/>
<br/>
<br/>
<br/>
<br/>
- Since the description of the second seco Overview <u>Micro-Fit 3.0 Connector System Product Family</u>

Product Literature Order No 987650-5984
Product Name Micro-Fit 3.0
UPC 800753839854

**Physical** 

Breakaway No Circuits (Loaded) 18 Circuits (maximum) 18 Color - Resin Black Durability (mating cycles max) 30 Flammability 94V-0 Glow-Wire Capable Yes Lock to Mating Part Yes Mated Height 17.64mm Material - Metal **Brass** Material - Plating Mating Tin Material - Plating Termination Tin

Material - Resin High Temperature Thermoplastic

Net Weight 2.443/g Number of Rows Orientation Vertical PC Tail Length 3.18mm **PCB** Locator Yes **PCB** Retention None PCB Thickness - Recommended 1.60mm Packaging Type Tray Pitch - Mating Interface 3.00mm Plating min - Mating 0.254µm Polarized to PCB Yes Shrouded Fully Stackable No Surface Mount Compatible (SMC) Yes

Temperature Range - Operating -40° to +105°C
Termination Interface: Style Through Hole

**Electrical** 

Current - Maximum per Contact 8.5A Voltage - Maximum 600V

**Solder Process Data** 

Duration at Max. Process Temperature (seconds) 030

Lead-freeProcess Capability SMC&WAVE

Max. Cycles at Max. Process Temperature 003 Process Temperature max. C 260

**Material Info** 

**Reference - Drawing Numbers** 

Packaging Specification PK-70873-0314-001

Product Specification PS-43045, PS-43045-001, TS-43045-001-001,

TS-46235-001-001 SD-43045-010

Sales Drawing SD-43045-010 Symbol/Footprint Data SYM-43045-1827 Test Summary 430450004-TS-000

This document was generated on 03/15/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION