

## This document was generated on 03/26/2019 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: Status:	0430452401 Active			
Overview:   Micro-Fit 3.0 Connector System Product Family     Description:   Micro-Fit 3.0 Right-Angle Header, 3.00mm Pitch, Dual Row, 24 Circuits, with S     Plastic Peg PCB Lock, Gold, Glow-Wire Capable, Black				
Documents: 3D Model Drawing (PDF) Product Specification Product Specification Product Specification		Product Specification TS-43045-002-001 (PDF) Product Specification TS-46235-001-001 (PDF) Packaging Specification PK-70873-0313-001 (PDF) RoHS Certificate of Compliance (PDF) Product Literature (PDF)	Series image	e - Reference only
Agency Certification CSA UL General Product Family Series Application Comments		LR19980 E29179 PCB Headers <u>43045</u> Power, Wire-to-Board """"""""High Temperature Square Pin Solder	EU ELV Not Relevant EU RoHS Compliant REACH SVHC Not Contained Per -ED/88/2018 (15 January 2019) Halogen-Free	<u>China RoHS</u>
Comments		High Temperature Square Pin Solder Type <p><p>This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13 b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <p><p> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end- use standard(s). <p> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options. """""" High Temperature  Square Pin Solder Type<p><p>This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13 b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <p><p> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end- use standard(s). <p> If it is determined during the</p></p></p></p></p></p></p></p></p></p>	Status   Low-Halogen   For more information   China ROHS   ELV   ROHS Phthalates   Search Parts in the 43045 Series   Mates With   Micro-Fit 3.0 Received	n, please visit <u>Contact US</u> Green Image Not Relevant Not Contained his Series ptacle Housing <u>43025</u> TPA Receptacle Housing

Overview Product Literature Order No Product Name UPC

## Physical

1	FilySical	
	Breakaway	No
	Circuits (Loaded)	24
	Circuits (maximum)	24
	Color - Resin	Black
	Durability (mating cycles max)	30
ĺ	Flammability	94V-0
ĺ	Glow-Wire Capable	Yes
I	Mated Height	10.29mm
	Material - Metal	Brass
	Material - Plating Mating	Gold
l	Material - Plating Termination	Tin
l	Material - Resin	High Temperature Thermoplastic
	Net Weight	3.619/g
	Number of Rows	2
	Orientation	Right Angle
	PCB Locator	Yes
	PCB Retention	Yes
	PCB Thickness - Recommended	1.60mm
	Packaging Type	Tray
l	Pitch - Mating Interface	3.00mm
l	Plating min - Mating	0.381µm
l	Polarized to PCB	Yes
	Shrouded	Fully
	Stackable	No
	Surface Mount Compatible (SMC)	Yes
	Temperature Range - Operating	-40° to +105°C
	Termination Interface: Style	Through Hole
	<b>-</b>	-
	Electrical	
	Current - Maximum per Contact	8.5A
	Voltage - Maximum	600V
	Solder Process Data	
	Duration at Max. Process Temperature (seconds)	030
	Lead-freeProcess Capability	SMC&WAVE
	Max. Cycles at Max. Process Temperature	003
	Process Temperature max. C	260
		200
	Material Info	
	Reference - Drawing Numbers	
	Packaging Specification	PK-70873-0313-001
	Product Specification	PS-43045, PS-43045-001, TS-43045-001-001,
	·	TS-43045-002-001, TS-46235-001-001
	Sales Drawing	SD-43045-001
	Symbol/Footprint Data	SYM-43045-2400
1		

This document was generated on 03/26/2019 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.""""""""

Micro-Fit 3.0 Connector System Product Family

987650-5984

Micro-Fit 3.0

800754376310