

This document was generated on 03/15/2019 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: Status: Overview: Description: Documents:	0436501016 Active <u>Micro-Fit 3.0 Connector System Product Family</u> Micro-Fit 3.0 Vertical Header, 3.00mm Pitch, Single Row, 10 Circuits, with PCB Polarizing Peg, Gold, Glow-Wire Capable, Black		A A A A A A A A A A A A A A A A A A A	
	<u>P3</u> PS-43650 (PDF) R(roduct Specification TS-46235-001-001 (PDF) ackaging Specification PK-70873-0811 (PDF) oHS Certificate of Compliance (PDF) roduct Literature (PDF)	Series image	- Reference only
Agency Certification CSA UL General Product Family Series Application Comments	PCE 436 Pow """"" proc folio a) A leas Wire per requ IEC elec to h proc theii acco wire any it is suita con """" proc folio a) A leas Wire per requ IEC elec to h proc theii acco wire any it is suita con """"	19980 179 3 Headers 50 ver, Wire-to-Board ""High Temperature Square Pin <p><p>This Molex duct is manufactured from material that has the owing ratings, tested by independent agencies:. A Glow Wire Ignition Temperature (GWIT) of at st 775 deg C per IEC 60695-2-13 b) A Glow e Flammability Index (GWFI) above 850 deg C IEC 60695-2-12.and hence complies with the uirements set out in the International Standard 60335-1 5th edition - household and similar ctrical appliances - safety, section 30 Resistance eat and fire. <p><p> The customers using this duct must determine its suitability for use in r particular application through testing or other eptable means as described in end-product glow- a flammability test standard IEC 60695-2-11 and applicable product end-use standard(s). <p> If determined during the customer's evaluation of ability, that higher performance is required, please tact Molex for possible product options.""""" ""High Temperature Square Pin<p>>P>This Molex duct is manufactured from material that has the wing ratings, tested by independent agencies:. A Glow Wire Ignition Temperature (GWIT) of at st 775 deg C per IEC 60695-2-13 b) A Glow e Flammability Index (GWFI) above 850 deg C IEC 60695-2-12.and hence complies with the uirements set out in the International Standard IEC 35-1 5th edition - household and similar electrical liances - safety, section 30 Resistance to heat (fire. <p><p> The customers using this product st determine its suitability for use in their particular lication through testing or other acceptable means described in end-product glow-wire flammability test hoard IEC 60695-2-11 and any applicable product -use standard(s). <p> If it is determined during customer's evaluation of suitability, that higher</p></p></p></p></p></p></p></p></p>	China ROHS ELV RoHS Phthalates Search Parts in th 43650 Series Mates With Micro-Fit 3.0 Rece	China RoHS please visit Contact US Green Image Not Relevant Not Contained sSeries Dtacle Housing <u>43645</u> PA Receptacle Housing

Overview Product Literature Order No Product Name UPC

Physical				
Breakaway	No			
Circuits (Loaded)	10			
Circuits (maximum)	10			
Color - Resin	Black			
Durability (mating cycles max)	30			
Flammability	94V-0			
Glow-Wire Capable	Yes			
Mated Height	17.27mm			
Material - Metal	Brass			
Material - Plating Mating	Gold			
Material - Plating Termination	Tin			
Material - Resin	High Temperature Thermoplastic			
Net Weight	1.589/g			
Number of Rows	1			
Orientation	Vertical			
PCB Locator	Yes			
PCB Retention	Yes			
PCB Thickness - Recommended	1.60mm			
Packaging Type	Tray			
Pitch - Mating Interface	3.00mm			
Plating min - Mating	0.381µm			
Plating min - Termination	2.540µm			
Polarized to PCB	Yes			
Shrouded	Fully			
Stackable	No			
Surface Mount Compatible (SMC)	Yes			
Temperature Range - Operating	-40° to +105°C			
Termination Interface: Style	Through Hole - Kinked Pin			
-				
Electrical	0.54			
Current - Maximum per Contact	8.5A			
Voltage - Maximum	600V			
Solder Process Data				
Duration at Max. Process Temperature (seconds)	030			
Lead-freeProcess Capability	SMC&WAVE			
Max. Cycles at Max. Process Temperature	003			
Process Temperature max. C	260			
	200			
Material Info				
Reference - Drawing Numbers				
Packaging Specification	PK-70873-0811			
Product Specification	PS-43650, TS-43045-001-001, TS-43045-002-001,			
	TS-46235-001-001			
Sales Drawing	SD-43650-006			
Symbol/Footprint Data	SYM-43650-1015			

This document was generated on 03/15/2019 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

performance is required, please contact Molex for possible product options.""""""""

Micro-Fit 3.0 Connector System Product Family

987650-5984

Micro-Fit 3.0

800754835008