

## R18PD5-0 | 18V Cordless Brushless Percussion Drill



- Brushless percussion drill ideal for drilling in wood or metal, driving screws or even drilling in masonry thanks to the hammer function.
- Ryobi's Brushless technology uses patented electronics to deliver more runtime and power.
- e-Torque control automatically drives screws flush for a perfect finish every time.
- 13mm ratcheting chuck for improved bit gripping strength and durability.
- 2 gears to control the max speed to match different materials and applications.
- LED lights up your work area for better visibility.

	R18PD5-0
Charger included?	No
Chuck capacity (mm)	13
Max drilling steel (mm)	13
Max. drilling masonry (mm)	13
Max. drilling wood (mm)	32
Max. percussion rate (bpm)	6800 / 23800
Max. torque (Nm)	50
No load speed (rpm)	0-400 / 0-1400
No. of batteries supplied	0
Power	18V
Sound power level [dB(A)]	94.5
Sound power level uncertainty [dB(A)]	3.0
Sound pressure level (dB(A))	83.5
Sound pressure level uncertainty [dB(A)]	3.0
Supplied in	Recyclable Carton
Torque settings	Automatic
Vibration drilling into concrete [m/s <sup>2</sup> ]	13.9
Vibration drilling into concrete uncertainty [m/s <sup>2</sup> ]	1.5
Vibration drilling into Metal [m/s <sup>2</sup> ]	<2.5
Vibration drilling into metal uncertainty [m/s <sup>2</sup> ]	1.5
Vibration screw driving [m/s <sup>2</sup> ]	<2.5
Vibration screw driving uncertainty [m/s <sup>2</sup> ]	1.5
Weight (without battery) [Kg]	1.1
Weight with battery pack (kg)	1.5