

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022124052

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK 254 Wire-to-Board Header, Right-Angle, with Friction Lock, 5 Circuits

Documents:

3D Model

Packaging Specification PK-7478-001-000 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PS-99020-0088-001 (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	7395
Application	Signal, Wire-to-Board
Overview	KK® Interconnect System - Molex
Product Name	KK 254
UPC	800753728622
Physical	
Breakaway	No
Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Natural (White)
Durability (mating cycles max)	100
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	0.660/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.80mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Polarized to PCB	Yes
Shrouded	Partial
Stackable	No
Temperature Range - Operating	See Product Specification
Termination Interface: Style	Through Hole

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per

-ED/88/2018 (15

January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

7395 Series

Mates With

2695 KK Crimp Terminal Housing, 6471

KK Crimp Terminal Housing, 7720 KK IDT

Double Cantilever

Current - Maximum per Contact	4.0A
Voltage - Maximum	500V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Engineering Number	739505BG
Reference - Drawing Numbers	
Packaging Specification	PK-7478-001-000
Product Specification	PS-99020-0088-001
Sales Drawing	SD-7395-001

This document was generated on 03/26/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION