


KEMET Part Number: T529P226M010AAE200
(TEGPSP21A226M8R)

T529, Tantalum, Polymer Tantalum, Reduced Volume, 22 uF, 20%, 10 VDC, SMD, Polymer, Substrate, 200 mOhms, 2012, Height Max = 1mm



General Information

Supplier:	KEMET
Series:	T529
Dielectric:	Polymer Tantalum
Style:	SMD Chip
Description:	SMD, Polymer, Substrate
Features:	Substrate
RoHS:	Yes
Termination:	Gold
Shelf Life:	52 Weeks
MSL:	3

Dimensions

Footprint	2012
L	2mm +/-0.1mm
W	1.25mm +/-0.1mm
H	1mm MAX
S	0.55mm +/-0.1mm
F	0.9mm +/-0.1mm

Packaging Specifications

Weight:	11.4 mg
Packaging:	T&R, 178mm
Packaging Quantity:	3000

Specifications

Capacitance:	22 uF
Capacitance Tolerance:	20%
Voltage DC:	10 VDC (85C), 8 VDC (105C)
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	6.00% 120Hz 25C
Failure Rate:	N/A
Resistance:	200 mOhms (100kHz 25C)
Ripple Current:	354 mA (100kHz 45C), 318.6 mA (85C), 141.6 mA (105C)
Leakage Current:	66 uA (5min 25C)