



#### **Feature**

• Temperature range up to +105°C with load life of 2000 hours.


### **Specifications**

Items	Characteristics				
Capacitance Tolerance	± 20% (120Hz, 20°C)				
Operating Temperature Range	-55°C to +105°C				
Rated Voltage	100V				
Capacitance value	47μF				
Ripple Current	140mA rms at 105°C, 120Hz				
Surge Voltage	125V DC				
Leakage Current	47μA (After 2 minutes applica 3(μA), whichever is greater.)	tion of rated voltage, le	akage current	is not more than 0.01CV or	
	Measurement Frequency: 12	 20Hz. Temperature: 20	)°C		
Dissipation Factor (tan δ)	Rated Voltage(V)	100			
	tan δ(Max)	0.12			
	Measurement Frequency: 12				
Low Temperature Stability Impedance Ratio(Max)	Rated Voltage(V)	100			
	Z(-25°C)/Z(20°C)	3			
	Z(-40°C)/Z(20°C)	4			
	2000 hours,with application of rated voltage at 105°C				
1 1 : # -	Capacitance Change Within ±25% of Initial Value		l Value		
Load Life	tan δ	200% or less of Initial Specified Value			
	Leakage Current Initial Specified Value or less				
Shelf Life	After leaving capacitors under no load at 105°C for 1,000 hours, they meet the specified value for load life characteristics listed above.				
	The capacitors shall be kept on the hot plate maintained at 250°C for 30 seconds.  After removing from the hot plate and restored at		Capacitance Change	Within ± 10% of Initial Value	
Resistance to Soldering Heat			tan δ	Initial Specified Value	
Tiout	room temperature they mee requirements listed at right.	t the characteristics	Leakage Current	Initial Specified Value or less	
Applicable Standards	JIS C-5141 and JIS C-5102				





### **Dimensions**



D×L	Ø10×10.5
Α	3.2
В	10.3
С	10.3
E ±0.2	4.4
L	10.5

Dimensions: Millimetres

### **Electrical Characteristics**

Item		Te	est Method	Specification	
Rated Voltage					Voltage range, capacitance range, see specification of this series.
Capacitance  Dissipation factor	Measurir	ng frequency : 1 ng voltage : 1 ment circuit : 0	Voltage range, capacitance range, see specification of this series.  Dissipation factor, leakage current, see specification of this series.		
Leakage current	application 1000Ω res	on of the DC rated esistor at 20°C $\frac{1}{R}$ $\frac{1}{\sqrt{N}}$	be measured after d working voltage  CX  S1: Switch S2: Switch for prometer CX: Testing capacity	Dissipation factor leakage current, see specification of this series.	
	Step	Temperature	Storage Time		
	1	20 ±2°C	30 minutes		
	2	-40 ±3°C	2 hours		Step 2. Impedance ratio (Zr / Z <sub>r0</sub> )
	3	20 ±2°C	15 minutes		less than specified value. Step 4. Capacitance change :
Temperature	4	105 ±2°C	2 hours		within ± 20% of the initial
characteristics	Step 1. Measure the capacitance and impedance. (Z <sub>r0</sub> ) ( Z , 20°C, 120Hz ±10%) Step 2. Measure the impedance at thermal balance after 2 hours. ( Z , 20°C, 120Hz ±10%) Step 4. Measure the capacitance and leakage current at thermal balance after 2 hours.		measured value. Leakage current : Less than 10 times of initial specified value .		





Item	Test Method	Specification
Surge test	Rated surge voltage shall be applied (switch on) for $30 \pm 5$ seconds and then shall be applied (switch off) with discharge for $5 \pm 0.5$ min at room temperature . This cycle shall be repeated for $1000$ cycles. Duration of one cycle is $6 \pm 0.5$ minutes .	Capacitance change : within ± 20% of the initial specified value.  Dissipation factor : less than 200% of the initial specified value.
Applicable Ripple Current	The maximum A.C. current having frequency of 100k Hz which can be applied to the capacitor at 105 ±2°C continuously. Peak voltage not to exceed rated D.C. voltage.	Leakage current : within initial specified value.

### **Mechanical characteristics**

Item	Test Method				Specification		
	(A) Tensile strength : wire lead terminal :						
	d (mm)	≦0.45	0.5 ~ 0	3.8	0.8 <d td="" ≦1.25<=""><td>]</td><td></td></d>	]	
	Load (kg)	0.51	1		2	]	
	Snap-in termin	nal			,	-	
	d (mm)	snap-in	terminal				
	Load (kg)	:	2				
Lead strength	The capacitor shall withstand the constant tensile force specified between the body and each lead for 10 seconds without damage either mechanical or electrical.  (B) Bending strength:  wire lead terminal:					When the capacitance is measured, there shall be no intermittent contacts, or open- or	
Lead Strength	d (mm)	≦0.45	0.5 ~ (		0.8 <d td="" ≦1.25<=""><td> </td><td>short-circuiting.</td></d>		short-circuiting.
	Load (kg)	0.25	0.51		1	ļ	There shall be no such mechanical damage as terminal damage etc.
	Snap-in terminal						
	Cross section area of terminal			Force (kg)	ļ		
	0.	0.5 <s≦1< td=""><td>1</td><td></td><td></td></s≦1<>			1		
		S>1			2.5	]	
	With the capacitor in a vertical position apply the load specified axially to each lead. The capacitor shall be rotated slowly from the vertical to the horizontal position, back to the vertical position. The 90° in the opposite direction and back the original position. Performance of capacitor shall not have changed and leads shall be undamaged						
Vibration resistance	The frequency of the vibration shall vary uniformly within the range 10 to 55 Hz with the amplitude of 1.5mm, completing the cycle in the internal of one minute.  The capacitor shall be securely mounted by its leads with hold the body of capacitor. The capacitor shall be vibrated in three mutually perpendicular directions for a period of 2 hours in each direction.				oleting with rated in	Capacitance : no unsteady. Appearance : no abnormal. Capacitance change : within ± 5% of initial measured value .	
Solderability	The leads are dipped in the solder bath of Sn at 260 $\pm 5^{\circ}$ C for 2 $\pm$ 0.5 seconds . The dipping depth should be set at 1.5 $\sim$ 2mm .				The solder alloy shall cover the 95% or more of the dipped lead's area .		





### Reliability

Item	Test Method	Specification		
Soldering heat resistance	The leads immerse in the solder bath of Sn at 260 $\pm 5^{\circ}$ C for 10 $\pm 1$ seconds until a distance of 1.5 ~ 2mm from the case.	No damage or leakage of electrolyte. Capacitance change : within ± 10% of the initial measured value. Tan δ : less than specified value. Leakage current : less than specified value.		
Damp heat (Steady state )	Subject the capacitors to 40 ±2°C and 90% to 95% relative humidity for 240 ±8 hours.	Capacitance change : within ±10% of the initial measured value.  Tan δ : less than specified value.  Leakage current : less than specified value.		
Load life	After X hours continuous application of DC rated working voltage at 105 ±2°C, the measurements shall meet the following limits. Measurements shall be performed after 2 hours exposed at room temperature.	Standard of judgement is according to requirement of this series.		
Shelf life	After storage for Y hours at 105 ±2°C without voltage application, the measurements shall meet the following limits. Measurements shall be performed after exposed for 1 to 2 hrs at room temperature after application of DC rated voltage to the capacitor for Z minutes.			
Storage at Low Temperature	The capacitor shall be stored at temperature of -40 ±3°C for 240 ±8 hours, during which time no voltage shall be applied. And then the capacitor shall be subjected to standard atmospheric conditions for 16 hours or more, after which measurements shall be made.	Capacitance change : within ±10% of the initial value.  Tan δ : less than specified value.  Leakage current : less than specified value  Appearance : no abnormal.		

### **Frequency Correction Factor of Rated Ripple Current**

Frequency	50Hz	120Hz	300Hz	1kHz	10kHz
Coefficient	0.7	1	1.17	1.36	1.5

#### **Part Number Table**

Description	Part Number		
SMD Aluminium Electrolytic Capacitor	MCVVT100M470GB3L		

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

