

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0351500100](#)  
**Status:** **Active**  
**Overview:** [VersaBlade Wire-to-Wire Connector System](#)  
**Description:** Wire-to-Wire VersaBlade Hybrid Plug Housing, without Mounting Ears, 1 Circuit, Polyester UL94V-0, Natural

**Documents:**

[3D Model](#) [Packaging Specification PK-35150-001-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-35150-003-001 \(PDF\)](#)

**Agency Certification**

CSA LR19980  
 UL E29179

**General**

Product Family Crimp Housings  
 Series [35150](#)  
 Application Power, Wire-to-Wire  
 Comments Polarized to Mating Part, Positive Lock, Polarized to Mating Part, Positive Lock  
 Overview [VersaBlade Wire-to-Wire Connector System](#)  
 Product Name VersaBlade  
 UPC 800753876774


**Physical**

Breakaway No  
 Circuits (maximum) 1  
 Color - Resin Natural  
 Flammability 94V-0  
 Gender Plug  
 Glow-Wire Capable No  
 Keying to Mating Part None  
 Lock to Mating Part Yes  
 Material - Resin Polyester  
 Net Weight 1.153/g  
 Number of Rows 1  
 Packaging Type Bag  
 Panel Mount No  
 Pitch - Mating Interface N/A  
 Polarized to Mating Part Yes  
 Stackable No  
 Temperature Range - Operating -40° to +120°C

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification PK-35150-001-001  
 Product Specification PS-35150-003-001  
 Sales Drawing SD-35150-0100



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**  
**REACH SVHC**

Not Contained Per  
 -ED/88/2018 (15  
 January 2019)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[35150 Series](#)

**Mates With**

Receptacle Housing [351510110](#)

**Use With**

VersaBlade Crimp Terminals [35745](#) , TPA [35182](#)