



SAFETY DATA SHEET

Multi Screen Clene and Cloth

According to Preparation of Safety Data Sheets for Hazardous Chemicals Code of Practice, December 2011

SECTION 1: Identification: Product identifier and chemical identity

Product identifier

Product name Multi Screen Clene and Cloth

Product No. AMCA_200MIF, ZA

Relevant identified uses of the substance or mixture and uses advised against

Application Cleaning agent.

Uses advised against No specific uses advised against are identified.

Details of the supplier of the safety data sheet

Supplier GENERAL MANAGER
HK WENTWORTH PTY LIMITED
PO BOX 7336
WARRINGAH MALL
BROOKVALE NSW 2100
AUSTRALIA

SYNERGY ELECTRONICS LTD
39 RICHARD PEARSE DRIVE
AIRPORT OAKS
AUCKLAND 3045

AUSTRALIA TEL: +61 (0) 2 9938 1566, FAX: +61 (0) 2 9938 1467
NEW ZEALAND TEL: +64 (0) 9 836 6588, FAX: +64 (0) 9 836 9169
sales@hkwentworth.com.au

Emergency telephone number

Emergency telephone +61 2 8014 4558 (Australia)
+64 9 929 1483 (New Zealand)

SECTION 2: Hazard(s) identification

Classification of the substance or mixture

Physical hazards Not Classified

Health hazards Not Classified

Environmental hazards Aquatic Acute 3 - H402

Label elements

Hazard statements H402 Harmful to aquatic life.

Precautionary statements P273 Avoid release to the environment.
P501 Dispose of contents/ container in accordance with national regulations.

Other hazards

Multi Screen Clene and Cloth

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition and information on ingredients

Mixtures

Benzyl-C12-14-alkyldimethylammonium chlorides <1%

CAS number: —

M factor (Acute) = 10

M factor (Chronic) = 1

Classification

Acute Tox. 4 - H302

Skin Corr. 1B - H314

Eye Dam. 1 - H318

Aquatic Acute 1 - H400

Aquatic Chronic 1 - H410

Ethanol <1%

CAS number: 64-17-5

Classification

Flam. Liq. 2 - H225

The full text for all hazard statements is displayed in Section 16.

Composition comments None of the ingredients are required to be listed.

SECTION 4: First aid measures

Description of first aid measures

General information	If in doubt, get medical attention promptly. Show this Safety Data Sheet to the medical personnel.
Inhalation	No specific recommendations. If throat irritation or coughing persists, proceed as follows. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Loosen tight clothing such as collar, tie or belt. Get medical attention if any discomfort continues.
Ingestion	No specific recommendations. If throat irritation or coughing persists, proceed as follows. Rinse mouth. Get medical attention if any discomfort continues.
Skin Contact	No specific recommendations. Rinse with water. Get medical attention if any discomfort continues.
Eye contact	Rinse with water. Get medical attention if any discomfort continues.
Protection of first aiders	Use protective equipment appropriate for surrounding materials.

Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	No specific symptoms known. Spray/mists may cause respiratory tract irritation.
Ingestion	No specific symptoms known. May cause discomfort if swallowed.
Skin contact	No specific symptoms known. May cause discomfort.
Eye contact	No specific symptoms known. May be slightly irritating to eyes.

Multi Screen Clene and Cloth

Indication of any immediate medical attention and special treatment needed

Notes for the doctor	Treat symptomatically.
Specific treatments	No special treatment required.

SECTION 5: Firefighting measures

Extinguishing media

Suitable extinguishing media The product is not flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

Special hazards arising from the substance or mixture

Specific hazards Containers can burst violently or explode when heated, due to excessive pressure build-up.

Hazardous combustion products Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

Advice for firefighters

Protective actions during firefighting Avoid breathing fire gases or vapours. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapours and protect men stopping the leak.

Special protective equipment for firefighters Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Firefighter's clothing conforming to Australia/New Zealand Standards AS/NZS 4967 (for clothing) AS/NZS 1801 (for helmets), AS/NZS 4821 (for protective boots), AS/NZS 1801 (for protective gloves) will provide a basic level of protection for chemical incidents.

SECTION 6: Accidental release measures

Personal precautions, protective equipment and emergency procedures

Personal precautions No specific recommendations. For personal protection, see Section 8.

Environmental precautions

Environmental precautions Avoid discharge to the aquatic environment.

Methods and material for containment and cleaning up

Methods for cleaning up Reuse or recycle products wherever possible. Absorb spillage to prevent material damage. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. Dispose of contents/container in accordance with national regulations.

Reference to other sections

Reference to other sections For personal protection, see Section 8.

SECTION 7: Handling and storage, including how the chemical may be safely used

Precautions for safe handling

Usage precautions Keep out of the reach of children. Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimise spills. Keep container tightly sealed when not in use. Avoid the formation of mists. Avoid discharge to the aquatic environment.

Advice on general occupational hygiene Wash promptly if skin becomes contaminated. Take off contaminated clothing and wash before reuse. Wash contaminated clothing before reuse.

Multi Screen Clene and Cloth

Conditions for safe storage, including any incompatibilities

Storage precautions	No specific recommendations.
Storage class	Unspecified storage.
<u>Specific end use(s)</u>	
Specific end use(s)	The identified uses for this product are detailed in Section 1.

SECTION 8: Exposure controls and personal protection

Control parameters

Occupational exposure limits

Ethanol

Long-term exposure limit (8-hour TWA): 1000 ppm 1880 mg/m³

Exposure controls

Appropriate engineering controls	No specific ventilation requirements.
Eye/face protection	No specific eye protection required during normal use. Large Spillages: Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible.
Hand protection	No specific hand protection recommended.
Other skin and body protection	Appropriate footwear and additional protective clothing complying with an approved standard should be worn if a risk assessment indicates skin contamination is possible.
Hygiene measures	Wash hands thoroughly after handling. Do not eat, drink or smoke when using this product. Wash contaminated clothing before reuse.
Respiratory protection	No specific recommendations. Provide adequate ventilation. Large Spillages: If ventilation is inadequate, suitable respiratory protection must be worn.
Environmental exposure controls	Not regarded as dangerous for the environment.

SECTION 9: Physical and chemical properties

Information on basic physical and chemical properties

Appearance	Liquid.
Colour	Colourless.
Odour	No characteristic odour.
Odour threshold	Not available.
pH	Not available.
Melting point	Not available.
Initial boiling point and range	Not available.
Flash point	Not available.
Evaporation rate	Not available.
Evaporation factor	Not available.
Flammability (solid, gas)	Not available.
Flammability Limit - Lower(%)	Not available.

Multi Screen Clene and Cloth

Other flammability	Not available.
Vapour pressure	Not available.
Vapour density	Not available.
Relative density	0.997
Bulk density	Not available.
Solubility Value (g/100g H₂O 20°C)	Not available.
Partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.
Viscosity	Not available.
Explosive properties	Not considered to be explosive.
Oxidising properties	Does not meet the criteria for classification as oxidising.

SECTION 10: Stability and reactivity

Reactivity	There are no known reactivity hazards associated with this product.
Stability	Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.
Possibility of hazardous reactions	No potentially hazardous reactions known.
Conditions to avoid	There are no known conditions that are likely to result in a hazardous situation.
Materials to avoid	No specific material or group of materials is likely to react with the product to produce a hazardous situation.
Hazardous decomposition products	Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

SECTION 11: Toxicological information

Information on toxicological effects

Toxicological effects	Not regarded as a health hazard under current legislation.
<u>Acute toxicity - oral</u>	
Notes (oral LD₅₀)	Based on available data the classification criteria are not met.
<u>Acute toxicity - dermal</u>	
Notes (dermal LD₅₀)	Based on available data the classification criteria are not met.
<u>Acute toxicity - inhalation</u>	
Notes (inhalation LC₅₀)	Based on available data the classification criteria are not met.
<u>Skin corrosion/irritation</u>	
Animal data	Based on available data the classification criteria are not met.
<u>Serious eye damage/irritation</u>	

Multi Screen Clene and Cloth

Serious eye damage/irritation	Based on available data the classification criteria are not met.
<u>Respiratory sensitisation</u>	
Respiratory sensitisation	Based on available data the classification criteria are not met.
<u>Skin sensitisation</u>	
Skin sensitisation	Based on available data the classification criteria are not met.
<u>Germ cell mutagenicity</u>	
Genotoxicity - in vitro	Based on available data the classification criteria are not met.
<u>Carcinogenicity</u>	
Carcinogenicity	Based on available data the classification criteria are not met.
IARC carcinogenicity	Contains a substance/a group of substances which may cause cancer. IARC Group 1 Carcinogenic to humans.
<u>Reproductive toxicity</u>	
Reproductive toxicity - fertility	Based on available data the classification criteria are not met.
Reproductive toxicity - development	Based on available data the classification criteria are not met.
<u>Specific target organ toxicity - single exposure</u>	
STOT - single exposure	Not classified as a specific target organ toxicant after a single exposure.
<u>Specific target organ toxicity - repeated exposure</u>	
STOT - repeated exposure	Not classified as a specific target organ toxicant after repeated exposure.
<u>Aspiration hazard</u>	
Aspiration hazard	Based on available data the classification criteria are not met.
General information	No specific health hazards known. The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	No specific symptoms known. Spray/mists may cause respiratory tract irritation.
Ingestion	No specific symptoms known. May cause discomfort if swallowed.
Skin Contact	No specific symptoms known. May cause discomfort.
Eye contact	No specific symptoms known. May be slightly irritating to eyes.
Route of entry	Ingestion Inhalation Skin and/or eye contact
Target Organs	No specific target organs known.

Ethanol

Toxicological effects	Not regarded as a health hazard under current legislation.
<u>Acute toxicity - oral</u>	
Notes (oral LD₅₀)	LD ₅₀ 10470 mg/kg, Oral, Rat REACH dossier information. Based on available data the classification criteria are not met.
<u>Acute toxicity - inhalation</u>	
Notes (inhalation LC₅₀)	LD ₅₀ 124.7 mg/l, Inhalation, Rat REACH dossier information. Based on available data the classification criteria are not met.
<u>Skin corrosion/irritation</u>	

Multi Screen Clene and Cloth

Animal data	Dose: 0.2 mL, 24 hours, Rabbit Primary dermal irritation index: 0 REACH dossier information. Based on available data the classification criteria are not met.
<u>Skin sensitisation</u>	
Skin sensitisation	Local Lymph Node Assay (LLNA) - Mouse: Not sensitising. REACH dossier information. Based on available data the classification criteria are not met.
<u>Germ cell mutagenicity</u>	
Genotoxicity - in vitro	Gene mutation: Negative. REACH dossier information. Based on available data the classification criteria are not met.
Genotoxicity - in vivo	Chromosome aberration: Negative. REACH dossier information. Based on available data the classification criteria are not met.
<u>Carcinogenicity</u>	
IARC carcinogenicity	IARC Group 1 Carcinogenic to humans.
<u>Reproductive toxicity</u>	
Reproductive toxicity - fertility	Two-generation study - NOAEL 15% , Oral, Mouse REACH dossier information. Based on available data the classification criteria are not met.
Reproductive toxicity - development	Maternal toxicity: - NOAEL: 16000 ppm, Inhalation, Rat REACH dossier information. Based on available data the classification criteria are not met.
<u>Specific target organ toxicity - repeated exposure</u>	
STOT - repeated exposure	LOAEL ~4000 mg/kg, Oral, Rat REACH dossier information. Based on available data the classification criteria are not met.

SECTION 12: Ecological Information

Ecotoxicity	Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.
Toxicity	Based on available data the classification criteria are not met.

Ethanol

Toxicity	Based on available data the classification criteria are not met.
Acute toxicity - fish	LC ₅₀ , 96 hours: 14200 mg/l, Pimephales promelas (Fat-head Minnow)
Acute toxicity - aquatic invertebrates	LC ₅₀ , 48 hours: 5012 mg/l, Ceriodaphnia dubia
Acute toxicity - aquatic plants	EC ₅₀ , 72 hours: 11.5 mg/l, Chlorella vulgaris
Chronic toxicity - aquatic invertebrates	NOEC, 9 days: 9.6 mg/l, Daphnia magna

Persistence and degradability

Persistence and degradability The degradability of the product is not known.

Ethanol

Multi Screen Clene and Cloth

Persistence and degradability The substance is readily biodegradable.

Biodegradation Water - Degradation 74%: 10 days

Chemical oxygen demand 1.99 g O₂/g substance

Bioaccumulative potential

Bioaccumulative Potential No data available on bioaccumulation.

Partition coefficient Not available.

Ethanol

Bioaccumulative Potential Bioaccumulation is unlikely.

Partition coefficient log Pow: -0.35

Mobility in soil

Mobility No data available.

Ethanol

Mobility The product is soluble in water.

Surface tension 24.5 mN/m @ 20°C/68°F

Other adverse effects

Other adverse effects None known.

SECTION 13: Disposal considerations

Waste treatment methods

General information The generation of waste should be minimised or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way.

Disposal methods Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

SECTION 14: Transport information

General The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

UN number

Not applicable.

UN proper shipping name

Not applicable.

Transport hazard class(es)

No transport warning sign required.

Packing group

Not applicable.

Environmental hazards

Multi Screen Clene and Cloth

Environmentally hazardous substance/marine pollutant

No.

Special precautions for user

Not applicable.

Transport in bulk according to Not applicable.

Annex II of MARPOL 73/78
and the IBC Code

SECTION 15: Regulatory information

Inventories

Australia - AICS

None of the ingredients are listed or exempt.

SECTION 16: Any other relevant information

Training advice	Read and follow manufacturer's recommendations.
Issued by	Bethan Massey
Revision date	24/05/2016
Revision	1
SDS No.	206
Hazard statements in full	H225 Highly flammable liquid and vapour. H302 Harmful if swallowed. H314 Causes severe skin burns and eye damage. H318 Causes serious eye damage. H400 Very toxic to aquatic life. H402 Harmful to aquatic life. H410 Very toxic to aquatic life with long lasting effects.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.