

Section 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

Product name: MC001845 HARDENER

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC1: Adhesives, sealants.

1.3. Details of the supplier of the safety data sheet

Company name: Premier Farnell

150 Armley Road

Leeds

LS12 2QQ

Tel: +44 (0) 870 129 8608

Email: information@premierfarnell.com**1.4. Emergency telephone number**

Emergency tel: +44 (0) 870 202530

Section 2: Hazards identification**2.1. Classification of the substance or mixture**

Classification under CLP: Skin Irrit. 2: H315; Eye Irrit. 2: H319; Skin Sens. 1B: H317; Aquatic Chronic 3: H412

Most important adverse effects: Causes skin irritation. Causes serious eye irritation. May cause an allergic skin reaction.

Harmful to aquatic life with long lasting effects.

2.2. Label elements

Label elements:

Hazard statements: H315: Causes skin irritation.

H319: Causes serious eye irritation.

H317: May cause an allergic skin reaction.

H412: Harmful to aquatic life with long lasting effects.

Hazard pictograms: GHS07: Exclamation mark



Signal words: Warning

Precautionary statements: P261: Avoid breathing dust/fume/gas/mist/vapours/spray.

P273: Avoid release to the environment.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P302+P352: IF ON SKIN: Wash with plenty of water.

SAFETY DATA SHEET

MC001845 HARDENER

Page: 2

P333+P313: If skin irritation or rash occurs: Get medical advice/attention.

P305+P351+P338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P337+P313: If eye irritation persists: Get medical advice/attention.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

3-[3-(3-HYDROXYPROPOXY)-2,2-BIS[(3-HYDROXYPROPOXY)METHYL]PROPOXY]PROPAN-1-OL; 3-SULFANYLPROPANE-1,2-DIOL

EINECS	CAS	PBT / WEL	CLP Classification	Percent
615-735-8	72244-98-5	-	Skin Sens. 1B: H317; Aquatic Chronic 3: H412	70-90%

2,4,6-TRIS(DIMETHYLAMINOMETHYL)PHENOL - REACH registered number(s): 01-2119560597-27-XXXX

202-013-9	90-72-2	-	Acute Tox. 4: H302; Eye Irrit. 2: H319; Skin Irrit. 2: H315	10-30%
-----------	---------	---	---	--------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water. If irritation occurs or persists, seek medical attention. Transfer to hospital if necessary.

Eye contact: Immediately remove contact lenses if present. Bathe the eye with running water for 15 minutes. Get medical attention if any discomfort continues.

Ingestion: Do not induce vomiting. Wash out mouth with water. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Move to fresh air in case of accidental inhalation of vapours. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. There may be severe pain. The eyes may water profusely. The vision may become blurred.

Ingestion: There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Show this safety data sheet to the doctor in attendance. Eye bathing equipment should be available on the premises.

[cont...]

SAFETY DATA SHEET

MC001845 HARDENER

Page: 3

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Do not attempt to take action without suitable protective clothing - see section 8 of SDS. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Ensure adequate ventilation.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Ensure there is sufficient ventilation of the area. Avoid direct contact with the substance. Avoid the formation or spread of mists in the air.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): PC1: Adhesives, sealants.

Section 8: Exposure controls/personal protection

[cont...]

SAFETY DATA SHEET

MC001845 HARDENER

Page: 4

8.1. Control parameters

Workplace exposure limits: No data available.

DNEL/PNEC Values

Hazardous ingredients:

2,4,6-TRIS(DIMETHYLAMINOMETHYL)PHENOL

Type	Exposure	Value	Population	Effect
PNEC	Fresh water	84 ug/L	-	-
PNEC	Marine water	8.4 ug/L	-	-
PNEC	Microorganisms in sewage treatment	200 ug/L	-	-

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency. Suitable respiratory protection should be worn when there is inadequate ventilation.

Hand protection: Impermeable gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Impermeable protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Various

Odour: Mercaptan

Solubility in water: Insoluble

Flash point°C: >93

Relative density: 1.130

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

[cont...]

SAFETY DATA SHEET

MC001845 HARDENER

Page: 5

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong bases. Strong acids. Strong oxidising agents.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

2,4,6-TRIS(DIMETHYLAMINOMETHYL)PHENOL

DERMAL	RAT	LD50	1280	mg/kg
ORAL	RAT	LD50	1000	mg/kg
VAPOURS	RAT	4H LC50	>0.5	mg/kg

Relevant hazards for product:

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
Respiratory/skin sensitisation	-	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. There may be severe pain. The eyes may water profusely. The vision may become blurred.

Ingestion: There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Section 12: Ecological information

12.1. Toxicity

Hazardous ingredients:

[cont...]

SAFETY DATA SHEET

MC001845 HARDENER

Page: 6

2,4,6-TRIS(DIMETHYLAMINOMETHYL)PHENOL

Scenedesmus Subspicatus	72H ErC50	66	mg/l
ZEBRAFISH (Brachydanio rerio)	96H LC50	175	mg/l

12.2. Persistence and degradability

Persistence and degradability: No data available.

12.3. Bioaccumulative potential

Bioaccumulative potential: No data available.

12.4. Mobility in soil

Mobility: Insoluble in water.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Harmful to aquatic organisms.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Waste code number: 08 04 09

Disposal of packaging: Arrange for collection by specialised disposal company.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

* indicates text in the SDS which has changed since the last revision.

[cont...]

SAFETY DATA SHEET

MC001845 HARDENER

Page: 7

Phrases used in s.2 and s.3: H302: Harmful if swallowed.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H412: Harmful to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.

Section 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

Product name: MC001845 RESIN

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC1: Adhesives, sealants.

1.3. Details of the supplier of the safety data sheet

Company name: Premier Farnell

150 Armley Road

Leeds

LS12 2QQ

Tel: +44 (0) 870 129 8608

Email: information@premierfarnell.com**1.4. Emergency telephone number**

Emergency tel: +44 (0) 870 202530

Section 2: Hazards identification**2.1. Classification of the substance or mixture**

Classification under CLP: Skin Irrit. 2: H315; Eye Irrit. 2: H319; Skin Sens. 1: H317; Aquatic Chronic 2: H411; -: EUH205

Most important adverse effects: Causes skin irritation. Causes serious eye irritation. May cause an allergic skin reaction.

Toxic to aquatic life with long lasting effects. Contains epoxy constituents. May produce an allergic reaction.

2.2. Label elements

Label elements:

Hazard statements: H315: Causes skin irritation.

H319: Causes serious eye irritation.

H317: May cause an allergic skin reaction.

H411: Toxic to aquatic life with long lasting effects.

EUH205: Contains epoxy constituents. May produce an allergic reaction.

Hazard pictograms: GHS07: Exclamation mark

GHS09: Environmental



Signal words: Warning

Precautionary statements: P261: Avoid breathing vapours.

SAFETY DATA SHEET

MC001845 RESIN

Page: 2

P273: Avoid release to the environment.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P302+P352: IF ON SKIN: Wash with plenty of water.

P333+P313: If skin irritation or rash occurs: Get medical advice/attention.

P305+P351+P338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P337+P313: If eye irritation persists: Get medical advice/attention.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

BISPHENOL A EPOXY RESIN (MW <700) - REACH registered number(s): 01-2119456619-26-XXXX

EINECS	CAS	PBT / WEL	CLP Classification	Percent
500-033-5	25068-38-6	-	Skin Irrit. 2: H315; Eye Irrit. 2: H319; Skin Sens. 1: H317; Aquatic Chronic 2: H411	>90%

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact. May cause sensitisation in susceptible individuals.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises. Show this safety data sheet to the doctor in attendance.

[cont...]

SAFETY DATA SHEET

MC001845 RESIN

Page: 3

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. Mark out the contaminated area with signs and prevent access to unauthorised personnel.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): PC1: Adhesives, sealants.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

[cont...]

SAFETY DATA SHEET

MC001845 RESIN

Page: 4

DNEL/PNEC Values

Hazardous ingredients:

BISPHENOL A EPOXY RESIN (MW <700)

Type	Exposure	Value	Population	Effect
DNEL	Inhalation	12.25 mg/m ³	Workers	Systemic
DNEL	Dermal	8.33 mg/kg	Workers	Systemic
PNEC	Fresh water	6 ug/L	-	-
PNEC	Marine water	600 ng/L	-	-
PNEC	Microorganisms in sewage treatment	10 mg/L	-	-
PNEC	Fresh water sediments	996 ug/kg	-	-
PNEC	Marine sediments	99.6 ug/kg	-	-
PNEC	Soil (agricultural)	196 ug/kg	-	-
PNEC	Food chain	11 mg/kg	-	-

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. The floor of the storage room must be impermeable to prevent the escape of liquids.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Yellow

Odour: Perceptible odour

Viscosity: Viscous

Boiling point/range°C: >200

Flash point°C: 245

Relative density: 1..17

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

[cont...]

SAFETY DATA SHEET

MC001845 RESIN

Page: 5

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids. Amines. Alcohols.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

BISPHENOL A EPOXY RESIN (MW <700)

DERMAL	RAT	LD50	>2000	mg/kg
ORAL	RAT	LD50	>2000	mg/kg

Relevant hazards for product:

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
Respiratory/skin sensitisation	DRM	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact. May cause sensitisation in susceptible individuals.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information

[cont...]

SAFETY DATA SHEET

MC001845 RESIN

Page: 6

12.1. Toxicity

Hazardous ingredients:

BISPHENOL A EPOXY RESIN (MW <700)

Daphnia magna	48H EC50	1.7	mg/l
GREEN ALGA (Selenastrum capricornutum)	72H ErC50	2.4	mg/l
RAINBOW TROUT (Oncorhynchus mykiss)	96H LC50	1.2	mg/l

12.2. Persistence and degradability

Persistence and degradability: Not readily biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Toxic to aquatic organisms.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Waste code number: 08 04 09

Disposal of packaging: Arrange for collection by specialised disposal company.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN3082

14.2. UN proper shipping name

Shipping name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.
(BISPHENOL A EPOXY RESIN (MW <700))

14.3. Transport hazard class(es)

Transport class: 9

[cont...]

SAFETY DATA SHEET

MC001845 RESIN

Page: 7

14.4. Packing group

Packing group: III

14.5. Environmental hazards

Environmentally hazardous: Yes

Marine pollutant: Yes

14.6. Special precautions for user

Special precautions: No special precautions.

Tunnel code: E

Transport category: 3

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: EUH205: Contains epoxy constituents. May produce an allergic reaction.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H411: Toxic to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.