

600 V MDmeshTM DM6 fast-recovery SJ MOSFETs boost efficiency and robustness



MDmesh[™] DM6 fast-recovery body diode technology improves efficiency and system reliability thanks to new lifetime killing process

Combining an optimized capacitance profile and lifetime killing process that results in a low gate charge (Q_g) , very low recovery charge (Q_n) , low recovery time (t_n) and an excellent improvement in $R_{DS(on)}$ per area, the MDmeshTM DM6 MOSFET series is today's reference for full- and half-bridge topologies.

Thanks to our new MDmesh[™] DM6 series, power electronic designers are now ready for new scenarios targeting higher efficiency and very impressive power density for super robust power conversion topologies.

KEY FEATURES

- Extremely low R_{DS(on)}*area and Q_g and optimized capacitance profile for light load conditions
- Extremely high dv/dt
- Optimized body diode recovery phase
- Optimized softness

KEY BENEFITS

- Extremely high efficiency performance and increased power density
- More robust power conversion in ZVS, full and half bridge topologies
- Higher operation frequencies and better thermal management
- Reduced EMI

KEY APPLICATIONS


- Charging stations for electric vehicles
- LED lighting
- Telecom
- Servers
- Solar inverters

MDmesh[™] DM6 SERIES

600 V BVdss rated

ST's latest fast-recovery body diode super-junction MOSFET technology is optimized for ZVS, full- and half-bridge topologies. With a breakdown voltage of 600 V, MDmesh[™] DM6 power MOSFETs are available in a wide range of package options including a TO-Leadless (TO-LL) package solution, allowing efficient thermal management.

Efficiency test performed on 2 kW ZVS topology



AVAILABLE POWER TRANSISTORS IN OUR HIGH-VOLTAGE, SUPER-JUNCTION 600 V MDmesh™ DM6 SERIES

600 V MDmesh™ DM6 Product Plan											
R _{DS(on)} (Ω)	ld max (A)	Qg (nC)	trr (ns)	D²PAK	PowerFLAT	T0-220	T0-220FP	T0-247			TO-LL
					8x8 HV			Standard	Long Lead	Kelvin Pin	IO-LL
0.240 0.255**	15	18	85	STB22N60DM6*	STL22N60DM6*	STP22N60DM6*	STF22N60DM6*				
0.195 0.210**	18	23	92		STL26N60DM6*	STP26N60DM6*	STF26N60DM6*				
0.128 0.140**	25	35	100	STB33N60DM6*	STL33N60DM6*	STP33N60DM6*	STF33N60DM6*				
0.095 0.100**	30	44	105		STL45N60DM6*	STP45N60DM6		STW45N60DM6			
0.071	38	61	115					STW65N60DM6	STWA65N60DM6		ST065N60DM6*
0.054	48	80	124						STWA67N60DM6*		ST067N60DM6*
0.042	62	106	138					STW70N60DM6	STWA70N60DM6	STW70N60DM6-4*	
0.036	72	117	140					STW75N60DM6	STWA75N60DM6		

Note: * In development

** Refered to PowerFLAT™







To explore the complete MDmesh[™] DM6 product portfolio, visit www.st.com or use our ST-MOSFET-Finder mobile app for Android and iOS.



© STMicroelectronics - October 2018 - Printed in United Kingdom - All rights reserved The STMicroelectronics corporate logo is a registered trademark of the STMicroelectronics group of companies All other names are the property of their respective owners

