



DeoxIT® L260D Grease

Mechanical & Electrical Applications

DATA SHEET: DS-L260D.pdf
URL Link: https://goo.gl/2zebW3

1. Product Description: CAIG offers two types of standard DeoxIT® Greases (Lithium-based and Mineral-based)

DeoxIT® Greases are manufactured in semi-solid form for use as a combination cleaning, deoxidizing, protecting and lubricating preparation. Greases protect against oxidation (galvanic corrosion) and are free of mineral acids, sulphurs, alkalis and other noxious components aggressive to metals. DeoxIT® Greases improve performance of electrical contacts and mechanical components that require precise lubrication.

DeoxIT® Grease Type L260D - Lithium-based preparation. Good lubrication, excellent wear resistance, excellent pressure resistance, excellent oxidation (galvanic corrosion) protection, high dripping-point characteristics. Operating temperatures: -40°C to 260°C.

NEW! DeoxIT® Grease Type L260D - *Infused with DeoxIT® D-Series D100L* = Soft, thixotropic grease for lubrication and protection of surfaces. Maximum lubrication for relatively clean surfaces. The infusion of DeoxIT® D-Series D100L into the formulation provides an additional film on the metal surface to dissolve corrosion, improve conductivity and provide a moveable/flexible protective film on the surface.

See Technical Sheet: TB-DG260-17.pdf (https://goo.gl/aGj9UA),

Sales Sheet: C-L260-DN.pdf (https://goo.gl/NJwKHf).

2. Formulation: DeoxIT® Greases are offered with or without particles.

- **A.** NO particles (L260DNp) = Soft, thixotropic grease for lubrication and protection of surfaces. Maximum lubrication for relatively clean surfaces.
- **B.** *COPPER particles* (L260DCP) = Use when you require particles (conductive) to assist in oxide and corrosion breakup and good lubrication. Copper is conductive. Use in areas that two contacts will not touch and possibly short. Example: disconnect switches or large connectors and relays.
- **C.** ALUMINUM particles (L260DAp) = Use when aluminum metals are involved to assist break up corrosion. Use in areas that two contacts will not touch and possibly short. Example: aluminum rails, bolts, connectors.
- **D.** *GRAPHITE particles* (L260DGp) = Graphite provides excellent lubricating and heat transfer characteristics. Use where lubrication is vital and heat absorption and dissipation is important.
- **E.** QUARTZ particles (L260DQp) = Use when you need particles (<u>non conductive</u>) to assist in oxide break up and you require good lubrication and abrasion. Quartz particles assist in breaking up oxidation and corrosion. Quartz is nonconductive.







- **F.** *GRAPHITE/QUARTZ particles* (L260DGQp) = Use when heat transfer, lubrication and assistance is needed in breaking up oxides and corrosion. Finer particles than the copper.
- **G.** *TEFLON particles* (L260DTp) = Use when lubrication is essential. Teflon particles are nonconductive.
- **H.** CUSTOM FORMULATIONS = Contact a CAIG Associate; http://store.caig.com/s.nl/it.l/id.7/.f

3. Grease Comparison Chart:

Product	Heat	Wear	Water	Oxidation	Oxidation
	Resistance	Resistance	Resistance	Resistance*	Dissolving
DeoxIT® M260 DeoxIT® L260 DeoxIT® L260D Lithium Lithium Complex Complex Bentone Clay Polyurea Polyrex™	Excellent Very Good Excellent Good Very Good Very Good Very Good Very Good Excellent	Very Good Very Good Very Good Good Good Very Good Very Good	Good Very Good Excellent Good Excellent Excellent Good Excellent Good	Very Good Very Good Excellent Fair Fair Fair Good Good	Good Good Very Good Poor Poor Poor Poor Poor

^{*} Oxidation of lubricants can produce sludge, varnish, gum and acid.

4. Features/Benefits:

Good lubrication, good abrasion, excellent wear resistance, excellent pressure resistance, excellent oxidation (galvanic corrosion) protection, high dripping-point characteristics.

Superior moisture resistance. Resist washout and excessive dilution by water assuring all-weather protection. Excellent mechanical stability. Safe on plastics.

5. Uses:

Electrical:

Antenna connections, battery terminals, buss bars, commutators, conductor rails, conductors, contactors, disconnects, drying & processing equipment, high amperage/high voltage applications, industrial electrical equipment (lifts, cranes, robotics, etc.), power tools, relays & switches (heavy duty, knife, step, rotary), etc.

Mechanical:

Bearings (all types), doors (closures), drives (chain/sprockets), hatch closures, O-rings and seals, linear motion systems, plugs (threaded holes), rack & pinion assemblies, screw devices (jacks, rails), slide bushings, sliding parts, tracks/guides/rails, threaded closures, worm gears, etc.

[™] Polyrex is a trademark Of Exxon/Mobil Corporation























Audio/Video

Computers

Automotive Communications

Marine

Electrical

Energy

Photography

Security

Medical

Avionics

6. Types/Formulations/Part Numbers:

6a. Type: L260DNp (no particles)

> **Formulation:** 98.0% DeoxIT[®] L260Np Lithium Greas e

> > DeoxIT® D-Series D100L 2.0%

Part Nos.:

Sprays NEW! L260S-N10D 10 oz (284 g) spray (10.0 oz / 284 g)

L260-DN2G 100% squeeze tube 2 g L260-DN1 100% iar 28 g L260-DN8TP 100% grease tube 226 g L260-DN8 100% 226 g jar L260-DN360 100% pail 3.6 Kg

6b. Type: L260DAp (aluminum particles)

> Formulation: DeoxIT® L260Np Lithium Grease 95.0%

Aluminum particles, 600 grit (9 mm) 3.0%

2.0% DeoxIT® D-Series D100L

Part Nos.:

L260-DA2G 100% squeeze tube 2 g L260-DA1 100% jar 28 g L260-DA8TP 100% grease tube 226 g L260-DA8 100% jar 226 g L260-DA360 100% pail 3.6 Kg

6c. Type: L260DCp (copper particles)

> Formulation: 91.0% DeoxIT® L260Np Lithium Grease

> > 7.0% Copper particles, -150 mesh (-105 mm)

DeoxIT® D-Series D100L 2.0%

Part Nos.:

squeeze tube 2 g L260-DC2G 100% L260-DC1 100% 28 g jar L260-DC8TP 100% grease tube 226 g L260-DC8 100% jar 226 g L260-DC360 100% pail 3.6 Kg

6d. Type: L260DGp (graphite particles)

> DeoxIT® L260Np Lithium Grease Formulation: 95.0%

> > Graphite particles, -150 mesh (-105 mm) 3.0%

DeoxIT® D-Series D100L 2.0%

Part Nos.:

L260-DG2G 100% squeeze tube 2 g L260-DG1 100% 28 g jar L260-DG8TP 100% grease tube 226 g



Precision Lithium Grea





NEW Tube

(226 g)

NEW Retail Tube (28 g)





6e.





















Computers

Automotive Communications

Marine

Electrical

Energy

Photography

Security

Medical

Avionics

L260-DG8 L260-DG360

Formulation:

100% jar 100% pail

L260DQp

226 g 3.6 Kg

(quartz particles)

91.0% DeoxIT® L260Np Lithium Grease

7.0% Quartz particles, -200 mesh DeoxIT® D-Series D100L 2.0%

Part Nos.:

Type:

L260-DQ2G 100% squeeze tube 2 q L260-DQ1 100% jar 28 g L260-DQ8TP 100% grease tube 226 g 226 g L260-DQ8 100% jar L260-DQ360 100% 3.6 Kg pail

6f. L260DGQp (graphite/quartz particles) Type:

> Formulation: 91.0% DeoxIT® L260Np Lithium Grease

> > 2.0% Graphite

Quartz particles, -200 mesh 5.0% 2.0% DeoxIT® D-Series D100L

Part Nos.:

L260-DGQ2G 100% squeeze tube 2 q L260-DGQ1 100% jar 28 g L260-DGQ8TP 100% 226 g grease tube L260-DGQ8 100% 226 g iar L260-DGQ35 100% pail 3.6 Kg

Custom formulations available, contact CAIG associate. 6h.

Caulking Tube (226 g)



Small Pail (3.6 KG)



Pail (15.9 KG)

7. Directions for Use:

- 1. Turn off, unplug the device.
- 2. Clean/remove grease, dirt and other contaminations from the surfaces. Use a contact cleaner or degreaser (CAIG Labs., Part Nos. DCC-V510 or DDW-V610).
- 3. Select the DeoxIT® Grease (with or without particles) that is required for your application.
- 4. In extreme environmental conditions (salt, humidity, acidic, pollution), pre-treating with DeoxIT® D-Series (unless using DeoxIT® L260DNp Grease) may be recommended.
- 5. As an external environmental barrier (i.e. antenna connections, audio/video connections, etc.), apply liberally onto the entire surface.
- 6. For surface that require particles (i.e. disconnect knife switches, etc.), apply a small amount to the metal surfaces, then operate the switch to assist in break up of oxidation and corrosion. A second application may be required.
- 7. Turn on or energize the part/system.
- 8. For additional information or unique applications, contact a CAIG Associate; http://store.caig.com/s.nl/it.l/id.7/.f



8. Materials Compatibility (Plastics, Rubber, Elastomeric and Metals):

(Rating: Not compatible, Poor, Fair, Good, Excellent). (Compatibility testing is always recommended)

Material Name	Rating
ABS	Excellent
Nylon	Excellent
Lexan	Excellent
HDPE	Good
LDPE	Good
C.E.Phenolic	Excellent
Ероху	Excellent
Polycarbonate	Excellent
PMMA	Fair
POM	Excellent
PP	Excellent
PS	Fair
PTFE	Excellent
PVC	Excellent
TPE/Rubber/Varnish	Poor

Security

Medical

Avionics

IMPORTANT:

Rating: Any of the above that fall into the "Fair" and "Poor" categories should be thoroughly tested for compatibility. They may be compatible, however, it will depend on the manufacturing process of the materials. Acrylics, ABS, and polycarbonate, if under stress, may show slight cracking or crazing damage. Test for compatibility before use. On porous materials; i.e. wood, rubber, cloth, some phenolics, semi-cured materials, no liquid or solvents should be used. Occasionally, DeoxIT® will get onto unwanted surfaces, quickly wipe off surface and usually no damage will occur.

9. Technical Information/Specifications:

•					
TYPE:	M260	L260	TYPE:	M260	L260
Flow Point, min	-30°C	-30°C	Oil Type	Mineral	Synthetic Blend
Viscosity @ 100°F, SUS	763	785	Soap Type	None	Lithium-12 Hydroxy
ASTM Dropping Point	260°C	285°C	Soap %,		9.52
Specific Gravity @ 20°C	1.85	1.87	ASTM - Penetration	280	295
Flash Point	300°C	300°C	NLGI	2	2
¹ Lowest/Best Operating Temp. (general)	-30°C	-30°C	Deoxidizer	Yes	Yes
¹ Highest Operating Temp. (continuous duty)	200°C	200°C	Oxidation Inhibitor	Yes	Yes
Acid & Neutralization No. (mg KOH/g)	1.15	1.17	Corrosion Inhibitor	Yes	Yes
Saponification No. (mg KOH/g)	2.79	2.81	Texture	Buttery	Short Fiber
Electrical Conductivity (27°C) (10 ⁻¹² ohm ⁻¹ cm ⁻¹)	0.17	0.17	Color	Amber	Amber
² Dielectric Constant E _r	2.751	3.236	¹ Temperatures are conservative values for reference only.		
² Dielectric Strength E _d (kV/cm)		45.9	² NOTE: All values are relative to an ambient temperature of 26 to 28°C		
² Specific Insulation Resistance D (10 ¹² ohm-cm).	5.7 +.50/03	5.9 +.50/03	(approx. 80°F). Dielectric strength value is a statistical average taken from 10 measurings. Voltage measurement taken with 0.5% accuracy.		

Tests conducted on base material only. Greases with particles may have

different measurements.



10. Shipping and Additional Information:

DeoxIT® L260 and M260 Grease - Non aerosol:

No Shipping Restrictions Hazardous:

VOC (%): Less than 1%

DeoxIT® L260 and M260 Grease - Aerosols: (Part Nos. L260S-N10 and L260S-N10D)

Hazardous: Yes ORMD (No ground shipping restrictions)

VOC (%): 20.4%

11. Other Information:

YES **RoHS Compliant: VOC Compliant:** YES

MSDS Link, L260D http://caig.com/material-safety-data-sheets/ DeoxIT® Grease Sheet: http://caig.com/product-literature/#toggle-id-14 **CAIG Essential Guide:** http://caig.com/product-literature/#toggle-id-1 WHY DeoxIT® is Different: http://caig.com/product-literature/#toggle-id-12

12. MANUFACTURER DISCLAIMER:

To the best of our knowledge, the information contained herein is accurate. However, neither CAIG Laboratories, Inc., or any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. All materials may present unknown hazards and should be used with caution. In particular, improper use of our products and their inappropriate combination with other products and substances may produce harmful results which cannot be anticipated. Final determination of the suitability of any material is the sole responsibility of the user. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that may exist. All service performed on internal parts and equipment should be provided by qualified technicians.

13. Contact Information:



Website: www.caig.com

www.deoxit.com

General email: info@caig.com Technical email: tech@caig.com North America (Headquarters):

CAIG Laboratories, Inc.

12200 Thatcher Court Poway, CA 92064 USA Tel: (858) 486-8388

Fax: (858) 486-8398

Distributors (Domestic & International):

http://store.caig.com/s.nl/sc.15/.f



CAIG Laboratories, Inc.

12200 Thatcher Court, Poway, CA 92064 U.S.A. **P:** 858/486-8388 **E:** info@caig.com

WEB: www.caig.com | www.deoxit.com

