

Eyes:

Skin:

Skin:

4.3

4.4

4.5

Symptoms of Overexposure:

Acute Health Effects:

Chronic Health Effects:

Inhalation:

Ingestion: Eyes:

some sensitive individuals.

Nausea, intestinal discomfort, vomiting and/or diarrhea.

concentrations of vapors can cause drowsiness, dizziness, headaches and nausea.

Overexposure in eyes may cause redness, itching and watering.

May also induce skin sensitization and respiratory hypersensitivity. Possible allergic dermatitis

None expected.

individuals.

SAFETY DATA SHEET

Page 1 of 5

SDS-E-CCS503 Prepared to OSHA, ACC, ANSI, NOHSC, WHMIS, GHS & 1272/2008/EC Standards SDS Revision Date: 11/1/2018 SDS Revision: 3.1 1. PRODUCT & COMPANY IDENTIFICATION 1 1 Product Name CAIG Brand SCREEN CLEANER, (P/N CCS-503) 1.2 Chemical Name 1.3 Synonyms CAIG Brand Screen Cleaner CAIG Brand Screen Cleaner (CCS-503 and CCS-503-1G) 1.4 Trade Names: Product Use: 1.5 **Electronics Cleaner** Distributor's Name: 1.6 CAIG Laboratories, Inc. 12200 Thatcher Court, Poway, CA 92064-6876 USA 1.7 Distributor's Address 1.8 Emergency Phone: CHEMTREC: +1 (703) 527-3887 / +1 (800) 424-9300 (CCN XXXXX) 1.9 Business Phone / Fax: +1 (800) 224-4123 2. HAZARDS IDENTIFICATION 2.1 Hazard Identification: This product is NOT classified as a HAZARDOUS SUBSTANCE or as DANGEROUS GOODS according to the classification criteria of NOHSC: 1088 (2004) and ADG Code (Australia). WARNING! CAUSES EYE IRRITATION. Classification: Eye Irrit. 2B 22 Label Elements: Hazard Statements (H): H320 - Causes eye irritation. Precautionary Statements (P): P264 - Wash thoroughly after handling. P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P337+P313 - If eye irritation persists: Get medical advice/attention. 2.3 Other Warnings: KEEP OUT OF REACH OF CHILDREN. 3. COMPOSITION & INGREDIENT INFORMATION EXPOSURE LIMITS IN AIR (mg/m3) ACGIH OSHA NOHSC maa ppm ppm FS-FS-FS-STEL CHEMICAL NAME(S) CAS No. RTECS No. EINECS No. TI V STFI TWA STEL PEAK PFI IDI H OTHER 7732-18-5 ZC0110000 231-191-2 60-100 NE NE NF NF NF NE NE NE WATER NA NA NA NA NA NF NF NF NA PROPRIETARY MIXTURE Eye Irrit. 2B; H320 4. FIRST AID MEASURES 4.1 First Aid: Ingestion: If ingested, do not induce vomiting. If product has been swallowed, drink plenty of water or milk IMMEDIATELY. If the patient is vomiting, continue to offer water or milk. Never give water or milk to an unconscious person. Contact the nearest Poison Control Center or local emergency number. Provide an estimate of the time at which the material was ingested and the amount of the substance that was swallowed. Eyes: Splashes are not likely; however, if product gets in the eyes, flush with copious amounts of lukewarm water for at least 15 minutes lifting upper and lower lids, occasionally. Wash thoroughly with soap and water. In case of contact, immediately flush skin with plenty of water for at Skin: least 15 minutes. Inhalation: Remove victim to fresh air at once. If breathing difficult, administer oxygen. If breathing stops give artificial respiration. Keep person warm, quiet and get medical attention. 4.2 Effects of Exposure: If product is swallowed, may cause nausea, vomiting and/or diarrhea. Ingestion: Moderately irritating to the eyes. Symptoms of overexposure may include redness, itching, irritation and

May be irritating to skin. The product can cause allergic skin reactions (e.g., rashes, welts, dermatitis) in

Symptoms of skin overexposure may include redness, itching, and irritation of affected areas. Frostbite

like symptoms. The product can cause allergic skin reactions (e.g., rashes, welts, dermatitis) in some

Non-irritating when used as directed. Moderate irritation to eyes and skin near affected areas. Additionally, high

Non-irritating when used as directed. Overexposure may trigger asthma-like symptoms in some sensitive individuals.



Page 2 of 5 **SDS-E-CCS503**

Prepared to OSHA, ACC, ANSI, NOHSC, WHMIS, GHS & 1272/2008/EC Standards SDS Revision: 3.1 SDS Revision Date: 11/1/2018

4.6		4. FIRST A	AID MEASU	RES –	cont'd	k					
-	Target Organs:	Eyes, Skin									
.7	Medical Conditions	Pre-existing dermatitis, other skin conditions, and disorders of the			of the	HEALTH				1	
	Aggravated by Exposure:	target organs (eyes, skin).				FLAMM		1			0
						PHYSIC					0
									ENT		U В
						PROTE(SKIN		ENI		_
						EIES	SKIN				
		5 FIRE	IGHTING N	IFΔSIII	RES						
5.1	Fire & Explosion Hazards:	5. FIREFIGHTING MEASURES This product is not flammable. However, if involved in a fire, this product may decompose at high temperatures to form toxic gases (e.g., CO,CO _X).									
5.2	Extinguishing Methods:	Water, Foam, CO ₂ , Dry Chemical.		to cool uno	pened c	ontainers.					
5.3	Firefighting Procedures:	Fight fires as for surrounding mate breathing apparatus (pressure-de after the fire is out. Use water sp fire upwind. Avoid spraying water Prevent runoff from fire control or any natural waterway. Firefighter pressure self-contained breathing decomposition products and oxygen	mand) and full property to cool fire-extended in the cool fire-extended in the cool fire extended in the cool fire extende	otective ge posed surf age contair ering sewe unker gear	ar. Kee faces and ners becomes, drain includin	ep contain d to protec ause of da s, drinking g NIOSH-	ers cool of person anger of g water s approved	until wel al. Figh boil-over supply, o d positive	t t	10)
		6. ACCIDENT	ΓAL RELEA	SE ME	ASUF	RES					
		Before cleaning any spill or lea Equipment. Plastic or rubber glov Small Spills: Wear appropriate primaterial such as vermiculite or swater or a material such as "sperplastic brooms, shovels, dustpans Large Spills: Keep incompatible or release. Isolate immediate haz done with minimal risk. Wear app	ves, respirator, eye totective equipmer and to soak up th edy dry" to soak u s) and place into a materials (e.g., org card area and keep	e protection at including e product a up material plastic con ganics such o unauthori	n and aportion and place and place . Sweep tainer or as oil) are zed pers	ron may be and proted e into a co o up mate plastic lin- away from onnel out	e require ctive eye ontainer rial using er within n spill. Si of area.	d for clea wear. U for later g non-sp another tay upwii Stop spi	an-up of se a no disposa arking in contained and life or rele	ilarge spon-comb Il. Do n materials er. away fro ease if it	oills usti ot ι s (e. om s can
		7. HANDLING					7 1				
7.1	Work & Hygiene Practices:	Do not eat, drink or smoke whe container(s). When used as intercontact is possible. Wash uninten	n handling this pinded, no addition	roduct. Co al protectiv	ontents on equipr	under pre					
7.2	Storage & Handling:	Use and store in a cool, dry, we sunlight. Avoid temperatures about damage. To avoid unintentional s	ll-ventilated location in the second location	on (e.g., lo way from i	cal exha	aust ventil ible subst					
7.3	Special Precautions:	Clean all spills promptly. Spilled n	naterial may prese	nt a slippin	g hazard	l					
.3	Special Precautions:			•	•						,
7.3		8. EXPOSURE CONT	ROLS & PE	•	AL PF		TION				
	Exposure Limits:			•	AL PF	ROTEC	TION	OSHA	1	OTHER	
			ROLS & PE	•	AL PF		TION	OSHA STEL	IDLH	OTHER	
1	Exposure Limits: ppm (mg/m³)	8. EXPOSURE CONT CHEMICAL NAME(S) NA	ROLS & PE ACGIH TLV STEL NA NA	RSON/ ES-TWA NF	AL PF NOHSC ES- STEL NF	ES- PEAK NF	PEL NA	STEL NA	NA		
1	Exposure Limits:	8. EXPOSURE CONT	ROLS & PE ACGIH TLV STEL NA NA s of product, provi	ES-TWA NF de adequat	NOHSC ES- STEL NF te ventila	ES- PEAK NF ation (e.g.,	PEL NA local exh	STEL NA	NA		Ens
.1	Exposure Limits: ppm (mg/m³) Ventilation & Engineering	8. EXPOSURE CONT CHEMICAL NAME(S) NA When working with large quantities	ROLS & PE ACGIH TLV STEL NA NA s of product, provicus ashbasin is availal in is required under protection authorized.	ES-TWA NF de adequat ble in case der typical vized per	NF te ventila of exposicircums U.S. O	ES- PEAK NF stition (e.g., sure to eye tances of SHA's ree	PEL NA local exhes. use or	NA naust ver handlin	NA ntilation g. If CFR		Ens
.1 .3.2 .3.3	Exposure Limits: ppm (mg/m³) Ventilation & Engineering Controls:	8. EXPOSURE CONT CHEMICAL NAME(S) NA When working with large quantities that an eyewash station, sink or wander that an eyewash station is sufficient to the eyewash station that are suffici	ROLS & PE ACGIH TLV STEL NA NA s of product, proviashbasin is availal n is required under protection author te regulations, or D IRRITATION PO mes when handling yewear when clear	ES-TWA NF de adequat ole in case der typical vized per the approp DTENTIAL ag large qu ning spills	NOHSC ES- STEL NF te ventila of expos circums U.S. O riate sta	ES-PEAK NF attion (e.g., sure to eye tances of SHA's reandards of protective (e.g., ≥ 1	PEL NA local exhes. use or quiremen Canada, e eyewea gallon (NA naust ver handlin t in 29 its prov	NA ntilation g. If CFR inces, safety of this		Ens
.1 .3.2	Exposure Limits: ppm (mg/m³) Ventilation & Engineering Controls: Respiratory Protection:	8. EXPOSURE CONT CHEMICAL NAME(S) NA When working with large quantities that an eyewash station, sink or wan large and the states of the st	ROLS & PE ACGIH TLV STEL NA NA s of product, provioushbasin is availal in is required under protection authorate regulations, or the regulations, or the regulations of least when clear documentate irritations of use. He quantities (e.g., ≥	RSON/ ES-TWA NF de adequat oble in case der typical vized per the approp DTENTIAL ng large qu ning spills ants. Dwever, ma 1 gallon (3	NOHSC ES- STEL NF te ventilate of exposicircums U.S. O viriate star uantities or leaks ay cause 3.8 L)), v	ES-PEAK NF ation (e.g., sure to eye tances of SHA's rendards of protective (e.g., ≥ 1 . Contact	PEL NA local ext ess. use or quiremen Canada, e eyewea gallon (lenses p ation in s er, nitrile	NA naust ver handlin t in 29 its prov	NA httilation g. If CFR inces, safety of this pecial nsitive rvious		Ens



Page 3 of 5 SDS-E-CCS503

Prepared to OSHA, ACC, ANSI, NOHSC, WHMIS, GHS & 1272/2008/EC Standards SDS Revision: 3.1 SDS Revision Date: 11/1/2018

9. PHYSICAL & CHEMICAL PROPERTIES 9 1 Appearance: Milky white liquid 9.2 Odor No odor Odor Threshold 9.3 NA 94 pH: NA 9.5 Melting Point/Freezing Point: NA 9.6 Initial Boiling Point/Boiling NA Range: 9.7 Flashpoint NA 9.8 Upper/Lower Flammability NA Limits: Vapor Pressure: 9.9 NA 9 10 Vapor Density NA 9 11 Relative Density: NA 9.12 Solubility Soluble Partition Coefficient (log Pow): 9.13 NA 9.14 Autoignition Temperature NA 9.15 Decomposition Temperature: NA 9.16 Viscosity: NA 9.17 Other Information: NA 10. STABILITY & REACTIVITY Stable under normal conditions; unstable with heat or contamination. 10.1 Stability 10.2 Hazardous Decomposition Oxides of carbon (CO, CO₂). 10.3 Hazardous Polymerization: Will not occur 10.4 Conditions to Avoid: Open flames, sparks, high heat, incompatible substances and direct sunlight. 10.5 Incompatible Substances: Avoid extreme heat and ignition sources. Store away from oxidizers. 11. TOXICOLOGICAL INFORMATION Routes of Entry: Absorption: YES Ingestion: 11.1 NO 11.2 Toxicity Data: This product has NOT been tested on animals to obtain toxicology data. Toxicology data, found in scientific literature, is available for some of the components of the product and is not presented in this document. 11.3 Acute Toxicity: See Section 4.4 Chronic Toxicity 11.4 This material may aggravate any pre-existing skin condition (e.g., dermatitis). 11.5 Suspected Carcinogen: This product does not contain any chemicals known to the State of California to cause cancer or other reproductive harm. For more information go to www.P65Warnings.ca.gov Reproductive Toxicity: 11.6 This product is not reported to produce reproductive toxicity in humans. Mutagenicity This product is not reported to produce mutagenic effects in humans Embryotoxicity This product is not reported to produce embryotoxic effects in humans Teratogenicity: This product is not reported to cause teratogenic effects in humans. Reproductive Toxicity: This product is not reported to cause reproductive effects in humans 11.7 Irritancy of Product See Section 4.2 11 8 Biological Exposure Indices: NE 11.9 Physician Recommendations: Treat symptomatically. 12. ECOLOGICAL INFORMATION 12.1 **Environmental Stability** There is no specific data available for this product 12.2 Effects on Plants & Animals: There are no specific data available for this product. 12.3 Effects on Aquatic Life: There are no specific data available for this product; however, very large releases of this product may be harmful or fatal to overexposed aquatic life. 13. DISPOSAL CONSIDERATIONS Waste Disposal: 13.1 Products covered by this SDS, in their original form, when disposed as waste, are considered non hazardous waste according to Federal RCRA regulations (40 CFR 261). Disposal should be in accordance with local, state and federal regulations. Dispose of in accordance with federal, state and local regulations Special Considerations: 13.2 NA



Page 4 of 5 SDS-E-CCS503

Prepared to OSHA, ACC, ANSI, NOHSC, WHMIS, GHS & 1272/2008/EC Standards SDS Revision: 3.1 SDS Revision Date: 11/1/2018

14. TRANSPORTATION INFORMATION The basic description (ID Number, proper shipping name, hazard class & division, packing group) is shown for each mode of transportation. Additional descriptive information may be required by 49 CFR, IATA/ICAO, IMDG and the CTDGR. 49 CFR (GND): **NOT REGULATED** 14.2 IATA (AIR): **NOT REGULATED** 14.3 IMDG (OCN): NOT REGULATED 14.4 TDGR (Canadian GND): **NOT REGULATED** ADR/RID (EU): 14.5 **NOT REGULATED** SCT (MEXICO): 14.6 **NOT REGULATED** ADGR (AUS): 14.7 **NOT REGULATED** 15. REGULATORY INFORMATION SARA Reporting Requirements: 15.1 This product does not contain any substances subject to SARA Title III, section 313 reporting requirements. SARA TPQ: 15.2 There are no specific Threshold Planning Quantities for the components of this product. TSCA Inventory Status: 15.3 The components of this product are listed on the TSCA Inventory. CERCLA Reportable Quantity: 154 15.5 Other Federal Requirements: NA Other Canadian Regulations: 15.6 This product has been classified according to the hazard criteria of the CPR and the MSDS contains all of the information required by the CPR. The components of this product are listed on the DSL/NDSL. None of the components of this product are listed on the Priorities Substances List. 15.7 State Regulatory Information: No ingredients in this product, present in a concentration of 1.0% or greater, are listed on any of the following state criteria lists: California Proposition 65 (CA65), Delaware Air Quality Management List (DE), Florida Toxic Substances List (FL), Massachusetts Hazardous Substances List (MA), Michigan Critical Substances List (MI), Minnesota Hazardous Substances List (MN), New Jersey Right-to-Know List (NJ), New York Hazardous Substances List (NY), Pennsylvania Right-to-Know List (PA), Washington Permissible Exposures List (WA), Wisconsin Hazardous Substances List (WI). This product does not contain any chemicals known to the State of California to cause cancer or other reproductive harm. For more information go to www.P65Warnings.ca.gov. Other Requirements: 15.8 16. OTHER INFORMATION WARNING! CAUSES EYE IRRITATION. Use only as directed. Keep out of reach of children. Avoid contact with eyes. 16.1 Other Information: In case of accident or if you feel unwell seek medical advice immediately (show the label where possible). If skin irritation occurs: get medical advice/attention. KEEP LOCKED UP AND OUT OF REACH OF CHILDREN. Terms & Definitions: See last page of this Safety Data Sheet. 16.3 Disclaimer This Safety Data Sheet is offered pursuant to OSHA's Hazard Communication Standard, 29 CFR §1910.1200. Other government regulations must be reviewed for applicability to this product. To the best of ShipMate's & CAIG Laboratories, Inc.'s knowledge, the information contained herein is reliable and accurate as of this date; however, accuracy, suitability or completeness is not guaranteed and no warranties of any type, either expressed or implied, are provided. The information contained herein relates only to the specific product(s). If this product(s) is combined with other materials, all component properties must be considered. Data may be changed from time to time. Be sure to consult the latest edition. 16.4 Prepared for: CAIG Laboratories, Inc. 12200 Thatcher Court Powav. CA 92064-6876 Tel: +1 (800) CAIG-123 (244-4123) Fax: +1 (858) 486-8398 fax http://www.caig.com/ 16.5 Prepared by: ShipMate. Inc. P.O. Box 787 Sisters, Oregon 97759-0787 USA Tel: +1 (310) 370-3600 Fax: +1 (310) 370-5700

http://www.shipmate.com



Page 5 of 5

SDS-E-CCS503

Prepared to OSHA, ACC, ANSI, NOHSC, WHMIS, GHS & 1272/2008/EC Standards

SDS Revision: 3.1

SDS Revision Date: 11/1/2018

DEFINITION OF TERMS

A large number of abbreviations and acronyms appear on a SDS. Some of these that are commonly used include the following:

GENERAL INFORMATION:

CAS No.	Chemical Abstract Service Number
RTECS No.	Registry of Toxic Effects of Chemical Substances Number
EINECS No.	European Inventory of Existing Commercial Chemical Substances Number

EXPOSURE LIMITS IN AIR:

ACGIH	American Conference on Governmental Industrial Hygienists
IDLH	Immediately Dangerous to Life and Health
NOHSC	National Occupational Health and Safety Commission (Australia)
OSHA U.S. Occupational Safety and Health Administration	
PEL	Permissible Exposure Limit
STEL	Short Term Exposure Limit
TLV	Threshold Limit Value
TWA	Time Weighted Average

FIRST AID MEASURES:

CPR	Cardiopulmonary resuscitation - method in which a person whose heart has
	stopped receives manual chest compressions and breathing to circulate blood
	and provide oxygen to the body.

HAZARDOUS MATERIALS IDENTIFICATION SYSTEM: HMIS

HEALTH, FLAMMABILITY & REACTIVITY RATINGS:

0	Minimal Hazard	
1 Slight Hazard		
2	Moderate Hazard	
3	Severe Hazard	
4	Extreme Hazard	



PERSONAL PROTECTION RATINGS:

Α			
В			
С	ELA	THE STATE OF THE S	
D		H.	
Е			
F	(Ell)	HA.	

G		ELA		
Н			H.	
I		ELA		
J			TOTAL	
K	9		(
Х	Consult y special h	our supe andling d	rvisor or irections.	SOPs for



OTHER STANDARD ABBREVIATIONS:

Carc	Carc Carcinogenic	
Irrit	Irritant	
NA	Not Available	
NR	No Results	
ND	Not Determined	
NE	Not Established	
NF	Not Found	
SCBA	Self-Contained Breathing Apparatus	
Sens	Sensitization	
STOT RE	Specific Target Organ Toxicity – Repeat Exposure	
STOT SE	STOT SE Specific Target Organ Toxicity – Single Exposure	

NATIONAL FIRE PROTECTION ASSOCIATION: NFPA

FLAMMABILI	TY LIMITS IN AIR:
Autoignition Temperature	Minimum temperature required to initiate combustion in air with no other source of ignition
LEL	Lower Explosive Limit - lowest percent of vapor in air, by volume, that will explode or ignite in the presence of an ignition source
UEL	Upper Explosive Limit - highest percent of vapor in air, by volume, that will explode or ignite in the presence of an ignition source

HAZARD RATINGS:

0	Minimal Hazard	FLAMMABILITY
1	Slight Hazard	\ \ \ \
2	Moderate Hazard	REACTIVITY
3	Severe Hazard	
4	Extreme Hazard	
ACD	Acidic	\sim 1 \times 2
ALK	Alkaline	
COR	Corrosive	─ / ▼ ₩ >
₩	Use No Water	HEALTH 🔪
ОХ	Oxidizer	SPECIAL
TREFOIL	Radioactive	PRECAUTIONS

TOXICOLOGICAL INFORMATION:

LD ₅₀	Lethal Dose (solids & liquids) which kills 50% of the exposed animals
LC ₅₀	Lethal concentration (gases) which kills 50% of the exposed animal
ppm	Concentration expressed in parts of material per million parts
TD _{Io}	Lowest dose to cause a symptom
TCLo	Lowest concentration to cause a symptom
TD _{io} , LD _{io} , & LD _o or	Lowest dose (or concentration) to cause lethal or toxic effects
TC, TCo, LCio, & LCo	
IARC	International Agency for Research on Cancer
NTP	National Toxicology Program
RTECS	Registry of Toxic Effects of Chemical Substances
BCF	Bioconcentration Factor
TL _m	Median threshold limit
log Kow or log Koc	Coefficient of Oil/Water Distribution

REGULATORY INFORMATION:

WHMIS	Canadian Workplace Hazardous Material Information System
DOT	U.S. Department of Transportation
TC	Transport Canada
EPA	U.S. Environmental Protection Agency
DSL	Canadian Domestic Substance List
NDSL Canadian Non-Domestic Substance List	
PSL	Canadian Priority Substances List
TSCA	U.S. Toxic Substance Control Act
EU	European Union (European Union Directive 67/548/EEC)
WGK	Wassergefährdungsklassen (German Water Hazard Class)

WORKPLACE HAZARDOUS MATERIALS IDENTIFICATION (WHMIS) SYSTEM:

0	®		(2)	\odot	®		
Class A	Class B	Class C	Class D1	Class D2	Class D3	Class E	Class F
Compressed	Flammable	Oxidizing	Toxic	Irritation	Infectious	Corrosive	Reactive

CLP/GHS (1272/2008/EC) PICTOGRAMS:

			\Diamond			\Diamond		*
GHS01	GHS02	GHS03	GHS04	GHS05	GHS06	GHS07	GHS08	GHS09
Explosive	Flammable	Oxidizer	Pressurized	Corrosive	Toxic	Harmful Irritating	Health Hazard	Environment