



## Main

Range of product	Harmony
Product or component type	Communication module
Communication port protocol	Modbus TCP network

## Complementary

Integrated connection type	Ethernet TCP/IP RJ45 - 2 twisted pairs - class D
Transmission rate	10/100 Mbit/s
Communication service	BOOTP Static IP DHCP (Modbus TCP/IP) DHCP (Modbus TCP/IP)
Web services	Web server
Physical interface	RJ45 - 10BASE-T RJ45 - 100BASE-TX
Memory description	User web page size 2 MB
Marking	CE
Local signalling	1 LED for transmission activity 1 LED for reception activity (RX) 1 LED for module status 1 LED for error
Product destination	Wireless access point ZBRN1
Product weight	0.044 kg

## Environment

product certifications	CSA UL 508 UL 873 BTL UL 60730-1
electromagnetic compatibility	EMC immunity conforming to EN/IEC 61000-6-1 EMC immunity level 2 conforming to EN/IEC 60730-1 EMC immunity level 2 conforming to EN/IEC 60730-1 Electrostatic discharge level 3B conforming to IEC 61000-4-2 Radiated RF fields level 3A conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test level 4B conforming to IEC 61000-4-4 Surge immunity test level 3 conforming to IEC 61000-4-5 Conducted RF disturbances level 3A conforming to IEC 61000-4-6 Conducted EMC level 2 conforming to EN/IEC 60730-1 Conducted EMC conforming to EN/IEC 61000-6-3 EMC immunity conforming to IEC 61800-3 Conducted EMC conforming to IEC 61800-3 category C1
IP degree of protection	IP20
ambient air temperature for operation	-20...65 °C
ambient air temperature for storage	-25...70 °C
relative humidity	5...95 % without condensation
pollution degree	2
operating altitude	0...2000 m
storage altitude	0...3048 m
vibration resistance	1.5 mm for 3...13 Hz 1 mm for 13...23 Hz 2 gn for 23...150 Hz
shock resistance	15 gn during 11 ms

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1402 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available