



### Main

Range of product	Harmony 9001SK
Product or component type	Pilot light
Device short name	9001SK
Lens type	Domed plastic
Light block supply	Direct

### Complementary

Bezel material	Plastic
Mounting diameter	30 mm
Shape of signaling unit head	Round
Cap/operator or lens colour	Amber
Light source	LED
Bulb base	BA 9s
[Us] rated supply voltage	120 V AC/DC
Tightening torque	0.8 N.m conforming to EN/IEC 60947-1
Shape of screw head	Cross slotted head
Connections - terminals	Screw clamp terminals (1 x 0.22...2 x 1.5 mm <sup>2</sup> ) conforming to EN/IEC 60947-1
[Ith] conventional free air thermal current	10 A
Short-circuit protection	10 A cartridge fuse conforming to EN/IEC 60947-5-1
[Ui] rated insulation voltage	250 V (degree of pollution: 2) conforming to EN/IEC 60947-1
[Uimp] rated impulse withstand voltage	2.5 kV conforming to EN/IEC 60947-1
Operating position	Any position
CAD overall width	54 mm
CAD overall height	70 mm
CAD overall depth	42 mm
Product weight	0.082 kg
Device presentation	Complete product

### Environment

electrical shock protection class	Class II conforming to IEC 61140
protective treatment	TC
IP degree of protection	IP66 conforming to IEC 60529
NEMA degree of protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 4X
vibration resistance	7 gn (f = 2...500 Hz) conforming to IEC 60068-2-6
shock resistance	50 gn conforming to IEC 60068-2-27
ambient air temperature for operation	-25...70 °C
ambient air temperature for storage	-40...70 °C
standards	EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4

JIS C 4520  
JIS C 852  
UL 508  
CSA C22.2 No 14

product certifications

NEMA  
UL 508

## Offer Sustainability

Sustainable offer status

785901425151

RoHS (date code: YYWW)

Compliant - since 0921 - Schneider Electric declaration of conformity

REACH

Reference not containing SVHC above the threshold


## Contractual warranty

Warranty period

18 months

## Dimensions

mm  
in.



e panel thickness: 1 to 6 mm / 0.04 to 0.24 in.