


VW3A5105

motor choke - 314 A - for variable speed drive
ATV61/ATV71 - IP00



Main

Product or component type	Motor choke
Range compatibility	Altivar 61 Altivar 71 Altivar 61Q Altivar 71Q
Product specific application	Output filter
[In] rated current	314 A
Product compatibility	ATV61HC11N4 ATV61HC13N4 ATV61HC20Y ATV61HD55M3X ATV61HD75M3X ATV71HC11N4 ATV71HC13N4 ATV71HC16Y ATV71HD55M3X ATV71HD75M3X ATV61QC13N4 ATV61QC16N4 ATV71QC11N4 ATV71QC13N4 ATV61HC25Y ATV61QC16Y ATV61QC20Y ATV71HC20Y ATV71QC13Y ATV71QC16Y
Sale per indivisible quantity	3
Electrical connection	Tag connector M10

Complementary

Motor cable length	<= 150 m shielded cable P motor 55...75 kW at 200...240 V 1 <= 300 m unshielded cable P motor 55...75 kW at 200...240 V 1 <= 150 m shielded cable P motor 110...132 kW at 380...480 V 1 <= 250 m unshielded cable P motor 110...132 kW at 380...480 V 1 <= 150 m shielded cable P motor 160...250 kW at 500...690 V 1 <= 250 m unshielded cable P motor 160...250 kW at 500...690 V 1 <= 250 m shielded cable P motor 160...250 kW at 500...690 V 2 <= 400 m unshielded cable P motor 160...250 kW at 500...690 V 2
DV/dt	500 V/μs max at 400 V 750 V/μs max at 500 V 1000 V/μs max at 690 V
Thermal losses	
Output frequency	100 Hz
Ambient air temperature for operation	-10...50 °C
Product weight	32 kg

Environment

IP degree of protection	IP00 IP20 (with kits VW3A9612,613)
ambient air temperature for storage	-25...70 °C

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.