


TITLE: 1 W 1GHZ BNC/m COAXIAL TERMINATION

LTR. C

DRAWING



General tolerances: +/- 0.5 mm

ELECTRICAL CHARACTERISTICS

FREQUENCY RANGE	: DC - 1GHz
IMPEDANCE	: 50 Ohms
DC RESISTANCE	: 50 Ohms ± 2%
AVERAGE POWER HANDLING	: 1 W at 25°C
PEAK POWER HANDLING	: 500 W (1 μs, 1%) at 25°C
V.S.W.R :	DC - 0.5 GHz : <= 1.08
	0.5 - 1 GHz : <= 1.15


MECHANICAL CHARACTERISTICS

CONNECTOR	: BNC male per MIL C 39012
MAXIMUM WEIGHT	: 15 grams

ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE RANGE (°C)	: -55 , +125
STORAGE TEMPERATURE RANGE (°C)	: -55 , +125

Power derating
Versus temperature



PEN
CAT

QUALITY Dpt App.
MO
B

PAGE
1/1

DATE
14.05.84

NAME
DP

LTR

REVISIONS

DATE

APP.