

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [5037640301](#)  
**Status:** **Active**  
**Overview:** [Pico-Lock Connector System](#)  
**Description:** 1.00mm Pitch Pico-Lock Crimp Housing, 1.50mm Mated Height, Positive Side Locks, 3 Circuits

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-503764-001-001 \(PDF\)](#) [Product Literature \(PDF\)](#)  
[Packaging Specification SPK-503764-001-001 \(PDF\)](#)

**General**

Product Family	Crimp Housings
Series	<a href="#">503764</a>
Application	Signal, Wire-to-Board
Comments	See Molex product specification PS-503764-001 for additional current de-rating information, See Molex product specification PS-503764-001 for additional current de-rating information
Overview	<a href="#">Pico-Lock Connector System</a>
Product Literature Order No	987650-9061
Product Name	Pico-Lock
UPC	191128847070

**Physical**

Circuits (maximum)	3
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	N/A
Lock to Mating Part	Yes
Material - Resin	High Temperature Thermoplastic
Net Weight	23.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C


**Electrical**

Current - Maximum per Contact	2.5A
-------------------------------	------

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	SPK-503764-001-001
Product Specification	PS-503764-001-001
Sales Drawing	SD-503764-001-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[503764](#) Series

**Mates With**

[503763](#) Pico-Lock Wire-to-Board Header

**Use With**

[503765](#) Pico-Lock Crimp Terminal