


XR2AA02K10

single-stage heavy duty screw limit switch XR2 - lthe
= 10 A - 2 C/O - 200 rpm



Main

Range of product	XR and XF
Product or component type	Single-stage heavy duty screw limit switch
Device short name	XR2
Product specific application	Liquid level control in pumping systems Position control of moving parts of hoisting or materials handling equipment
Material	Aluminium alloy (body housing) Plastic (cover)
Type of operator	Drive shaft, end fittings with sprocket key and washer
Maximum revolution speed	200 rpm of input drive shaft
Theoretical number of turns	10 of input drive shaft
Number of poles	1

Complementary

Mechanical durability	10000000 cycles
Number of turns	<= 6 of threaded shaft
Threaded shaft screw pitch	4 mm
Operating finger radius	40 mm
Length of developed helical travel	4 mm
Differential snap over angle	30 ° contact actuators measured at finger
Repeat accuracy	0.02 % on the tripping point
Number of teeth	16 (pinion C) 26 (pinion B) 49 (pinion A) 59 (pinion D)
Actual number of turns	11.739 (input drive shaft)
Contact operation	Snap action
[Ie] rated operational current	A300, AC-15 (Ue = 240 V, Ie = 3 A) conforming to EN/IEC 60947-5-1 Q300, DC-13 (Ue = 250 V, Ie = 0.27 A) conforming to EN/IEC 60947-5-1
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	500 V conforming to EN/IEC 60947-1 600 V conforming to CSA C22.2 No 14
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-1
Resistance across terminals	<= 25 MOhm
Short-circuit protection	10 A cartridge fuse type gG
Connections - terminals	Screw clamp terminals, connection capacity: 2 x 1.5 mm ² with or without cable end Screw clamp terminals, connection capacity: 2 x 2.5 mm ² without cable end
Electrical durability	10000000 cycles AC-15 50/60 Hz inductive at 12 V, 70 VA, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 10000000 cycles AC-15 50/60 Hz inductive at 127 V, 270 VA, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 10000000 cycles AC-15 50/60 Hz inductive at 220 V, 290 VA, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 10000000 cycles AC-15 50/60 Hz inductive at 24 V, 120 VA, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 10000000 cycles AC-15 50/60 Hz inductive at 380 V, 300 VA, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 10000000 cycles AC-15 50/60 Hz inductive at 48 V, 180 VA, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 10000000 cycles AC-15 50/60 Hz inductive at 500 V, 300 VA, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 10000000 cycles AC-15 50/60 Hz resistive at 12 V, 45 VA, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 10000000 cycles AC-15 50/60 Hz resistive at 127 V, 180 VA, operating rate 3600

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

0.5 EN/IEC 60947-5-1
3000000 cycles DC-13 resistive at 24 V, 120 W, operating rate 3600 cyc/h, load factor
0.5 EN/IEC 60947-5-1
3000000 cycles DC-13 resistive at 440 V, 45 W, operating rate 3600 cyc/h, load factor
0.5 EN/IEC 60947-5-1
3000000 cycles DC-13 resistive at 48 V, 110 W, operating rate 3600 cyc/h, load factor
0.5 EN/IEC 60947-5-1

Cable entry	2 entries tapped for Pg 13 cable gland, clamping capacity: 9...12 mm
-------------	--

Environment

standards	EN/IEC 60947-5-1
protective treatment	TC
ambient air temperature for operation	-25...70 °C
ambient air temperature for storage	-40...70 °C
shock resistance	50 gn for 11 ms
vibration resistance	> 5 gn (10...55 Hz)
IP degree of protection	IP54 conforming to EN/IEC 60529

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will be Compliant on 4Q2013 Will be Compliant on 4Q2013

Contractual warranty

Warranty period	18 months
-----------------	-----------
