

ZCKJ4104H29

limit switch body ZCKJ - rotary head w/o lever - plug-in - 2C/O - snap - M20



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch body with spring return rotary head
Device short name	ZCKJ
Body type	Plug-in body
Product compatibility	XCKJ
Body material	Metal
Cable entry	1 entry tapped for M20 x 1.5 cable gland
Number of poles	2
Contacts type and composition	2 C/O
Contact operation	Snap action
Number of steps	2 3 positions
Contacts material	Silver plated contacts

Complementary

Switch actuation	From left and right
Local display	Without
Electrical connection	Screw-clamp terminals, clamping capacity: 1 x 0.75...2 x 1.5 mm ²
Positive opening	Without
Minimum actuation speed	0.01 m/min
[Ie] rated operational current	3 A at 240 V, AC-15, A300 conforming to EN/IEC 60947-5-1 appendix A 0.27 A at 250 V, DC-13, Q300 conforming to EN/IEC 60947-5-1 appendix A
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	300 V conforming to UL 508 contact block 500 V degree of pollution 3 conforming to IEC 60947-1 contact block 300 V conforming to CSA C22.2 No 14 contact block
Resistance across terminals	0.25 mOhm conforming to IEC 60255-7 category 3
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60664 6 kV conforming to IEC 60947-1
Short-circuit protection	10 A by gG cartridge fuse
Electrical durability	5000000 cycles, DC-13 120 V, 4 W, operating rate: < 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 5000000 cycles, DC-13 24 V, 10 W, operating rate: < 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 5000000 cycles, DC-13 48 V, 7 W, operating rate: < 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C
Width	40 mm
Height	77 mm
Depth	44 mm
Product weight	0.31 kg
Terminals description ISO n°1	(11-12)NC (13-14)NO (21-22)NC (23-24)NO

Environment

IP degree of protection	IP66
IK degree of protection	IK07

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

ambient air temperature for operation	10...120 °C for high temperature
ambient air temperature for storage	10...120 °C
environmental characteristic	High temperature

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1440 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------