

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 4, pitch: 2.5 mm, connection method: Crimp connection, color: white

The figure shows a 3-position version

Your advantages

- ☑ White design: Stable color when welding and during use
- High current carrying capacity of 6 A in very compact dimensions
- M Inverted connector with pin contacts for touch-proof device outputs or free-hanging cable/cable connections
- ☑ Cost-effective connection of crimped conductors in large quantities
- ☑ Tools for manual and automatic crimping available as an option



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	250 pc
GTIN	4 055626 495651
GTIN	4055626495651
Weight per Piece (excluding packing)	0.560 g
Custom tariff number	85472000
Country of origin	Germany

Technical data

Item properties

Brief article description	Printed-circuit board connector
Plug-in system	COMBICON COMPACT PTSM
Type of contact	Male connector



Technical data

Item properties

Range of articles	PTCM 0,5/PI
Pitch	2.5 mm
Number of positions	4
Connection method	Crimp connection
Number of levels	1

Electrical parameters

Rated current	6 A
Rated insulation voltage (III/2)	160 V
Rated surge voltage (III/2)	2.5 kV

Connection capacity

Conductor cross section flexible	0.14 mm ² 0.75 mm ² (Maximum external diameter of the insulation 1.9 mm)
Conductor cross section AWG / kcmil	26 18 (Maximum external diameter of the insulation 1.9 mm)
Stripping length	4.1 mm 4.5 mm

Material data - housing

Insulating material	РА
Insulating material group	I
CTI according to IEC 60112	600
Flammability rating according to UL 94	V0
Glow wire flammability index GWFI according to EN 60695-2-12	850
Glow wire ignition temperature GWIT according to EN 60695-2-13	775
Temperature for the ball pressure test according to EN 60695-10-2	125 °C

Dimensions for the product

Length [1]	18.3 mm
Width [w]	11.7 mm
Height [h]	5 mm
Pitch	2.5 mm
Height (without solder pin)	5 mm
Dimension a	7.5 mm

Packaging information

Type of packaging	packed in cardboard
Pieces per package	250
Denomination packing units	Pcs.
Ambient conditions	
Ambient temperature (storage/transport)	-40 °C 70 °C



Technical data

Ambient conditions

Ambient temperature (assembly)	-5 °C 100 °C
Ambient temperature (operation)	-40 °C

Termination and connection method

Mechanical tests according to standard

Visual examinationTest passed IEC 60512-1-1:2002-02Dimensional testTest passed IEC 60512-1-2:2002-02Resistance of markingTest passed IEC 60068-2-70:1995-12ResultTest passedSpecificationIEC 60512-13-2:2006-02No. of cycles25Insertion strength per pos. approx.3 NWithdraw strength per pos. approx.2 N
Resistance of markingTest passed IEC 60068-2-70:1995-12ResultTest passedSpecificationIEC 60512-13-2:2006-02No. of cycles25Insertion strength per pos. approx.3 N
Result Test passed Specification IEC 60512-13-2:2006-02 No. of cycles 25 Insertion strength per pos. approx. 3 N
Specification IEC 60512-13-2:2006-02 No. of cycles 25 Insertion strength per pos. approx. 3 N
No. of cycles 25 Insertion strength per pos. approx. 3 N
Insertion strength per pos. approx. 3 N
Withdraw strength per pos. approx. 2 N
Polarization and coding Test passed IEC 60512-13-5:2006-02
Result Test passed
Specification IEC 60512-15-1:2008-05
Test force per pos. 20 N

Air clearances and creepage distances

Specification	IEC 60664-1:2007-04
Insulating material group	1
Voltage	160 V
Rated insulation voltage (III/3)	160 V
Rated insulation voltage (III/2)	160 V
Rated insulation voltage (II/2)	320 V
Rated surge voltage (III/3)	2.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV

Current carrying capacity / derating curves

Mechanical tests (A)

Insertion strength per pos. approx.	3 N
Withdraw strength per pos. approx.	2 N
Polarization when inserted requirement >20 N	Test passed
Contact holder in insert requirements >20 N	Test passed

Durability tests (B)

Specification	IEC 60512-9-1:2010-03
Contact resistance R ₁	3.2 mΩ



Technical data

Durability tests (B)

Insertion/withdrawal cycles	25
Contact resistance R ₂	3.4 mΩ
Impulse withstand voltage at sea level	2.95 kV
Power-frequency withstand voltage	1.39 kV

Climatic tests (D)

Specification	ISO 6988:1985-02	
Cold stress	-55 °C/2 h	
Thermal stress	105 °C/168 h	
Corrosive stress	$0.2 \text{ dm}^3 \text{SO}_2 \text{ on } 300 \text{ dm}^3/40 \text{ °C/1 cycle}$	
Impulse withstand voltage at sea level	2.95 kV	
Power-frequency withstand voltage	1.39 kV	


Environmental and durability tests (E)

Specification	IEC 61984:2008-10	
Result, degree of protection, IP code	Finger safety with IP20 test finger	

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e	
	No hazardous substances above threshold values	

Drawings



Type: PTCM 0,5/...-PL-2,5 WH with PTCM 0,5/...-PI-2,5 WH

Classifications

eCl@ss

eCl@ss 5.1	27260700
eCl@ss 6.0	27260700
eCl@ss 7.0	27440309



Classifications

eCl@ss

ecillass				
eCl@ss 8.0		27440309		
eCl@ss 9.0		27440309		
ETIM				
ETIM 6.0		EC002638		
Approvals				
Approvals				
Approvals				
cULus Recognized				
Ex Approvals				
Approval details				
cULus Recognized http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm E60425-20101209				
	D		В	
Nominal voltage UN	150 V		150 V	
Nominal current IN	5 A		5 A	
mm²/AWG/kcmil	22-18		22-18	

Accessories

Accessories

Crimp contact

Accessories - PTCM-MP-PI 0,34-0,75 R - 1013987



Crimp contact, type of contact: Male connector, connection method: Crimp connection, contact surface: Tin, type of packaging: Taped on roll



Accessories

Accessories - PTCM-MP-PI 0,14-0,5 R - 1013988



Crimp contact, type of contact: Male connector, connection method: Crimp connection, contact surface: Tin, type of packaging: Taped on roll

Accessories - PTCM-MP-PI 0,34-0,75 - 1013989



Crimp contact, type of contact: Male connector, connection method: Crimp connection, contact surface: Tin

Accessories - PTCM-MP-PI 0,14-0,5 - 1013990



Crimp contact, type of contact: Male connector, connection method: Crimp connection, contact surface: Tin

Crimping tool

Crimping pliers - CRIMPFOX-P CC 0.75 L - 1064998



Crimping pliers, for COMBICON crimp connectors with cross section: 0.14 ... 0.75 mm². Unlockable pressure lock, precise parallel crimping, front entry, B crimp, incl. 2 positioning aids

Additional products

Printed-circuit board connector - PTSM 0,5/ 4-P-2,5 WH - 1704857



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 4, pitch: 2.5 mm, connection method: Push-in spring connection, color: white, contact surface: Tin

03/15/2019 Page 6 / 8



Accessories

Feed-through header - PTSM 0,5/ 4-HHI-2,5-SMD WHR44 - 1707993



PCB headers, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 4, pitch: 2.5 mm, color: white, contact surface: Tin, mounting: SMD soldering, Article with anti-rotation pin

Feed-through header - PTSM 0,5/ 4-HHI0-2,5-SMD WHR44 - 1815219



PCB headers, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 4, pitch: 2.5 mm, color: white, contact surface: Tin, mounting: SMD soldering

Feed-through header - PTSM 0,5/ 4-HHI-2,5-THR WH R32 - 1815002



PCB headers, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 4, pitch: 2.5 mm, color: white, contact surface: Tin, mounting: THR soldering

Printed-circuit board connector - PTSM 0,5/ 4-PL-2,5 WH - 1709460



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 4, pitch: 2.5 mm, connection method: Push-in spring connection, color: white, contact surface: Tin

Printed-circuit board connector - PTCM 0,5/ 4-PL-2,5 WH - 1015462



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 4, pitch: 2.5 mm, connection method: Crimp connection, color: white



Phoenix Contact 2019 $\ensuremath{\mathbb{C}}$ - all rights reserved http://www.phoenixcontact.com