

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0010112093](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: KK 254 Crimp Housing, High Pressure, 9 Circuits, Natural

Documents:

[3D Model](#) [Packaging Specification PK-7880-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-7879-001 \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Crimp Housings
 Series [7880](#)
 Application Signal, Wire-to-Board
 Overview [KK® Interconnect System - Molex](#)
 Product Name KK 254
 UPC 800754241434

Physical

Circuits (maximum) 9
 Color - Resin Natural (White)
 Flammability 94V-0
 Gender Receptacle
 Glow-Wire Capable No
 Material - Resin Nylon
 Net Weight 0.882/g
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 2.54mm
 Pitch - Termination Interface 2.54mm
 Stackable No
 Temperature Range - Operating See Product Specification

Solder Process Data


Lead-freeProcess Capability N/A

Material Info

Engineering Number 7880-09B

Reference - Drawing Numbers

Packaging Specification PK-7880-001-001
 Product Specification PS-7879-001
 Sales Drawing SD-7880



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/88/2018 (15
 January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[7880 Series](#)

Mates With

KK254 PCB Headers [42375](#) , [42377](#) , [42376](#)
 , [4030](#) , [6373](#) , [6410](#)

Use With

[7879](#) KK High Pressure Crimp Terminal