

This document was generated on 03/18/2019 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Description: Micro-Fit 3.0 Vertica	e <u>ctor System Product Family</u> al Header, 3.00mm Pitch, Dual Row, 22 Circuits, with PCB d, Glow-Wire Capable, Black	
Documents: <u>3D Model</u> <u>Drawing (PDF)</u> <u>Product Specification PS-43045 (PDF)</u> <u>Product Specification PS-43045-001 (PDF)</u> <u>Product Specification TS-43045-001-001 (F</u>		Series image - Reference only
Agency Certification CSA UL General Product Family Series Application Comments	LR19980 E29179 PCB Headers 43045 Power, Wire-to-Board """"" High Temperature[Square Pin]Offset Through Hole Mounting]Solder Type <p><p>This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12. and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <p><p> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <p> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options."""" "Itigh Temperature[Square Pin]Offset Through Hole Mounting]Solder Type<p><p>This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13 b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60035-15 th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <p><p> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-</p></p></p></p></p></p></p></p></p>	EU ELV Not Relevant EU RoHS Compliant REACH SVHC Not Contained Per -ED/88/2018 (15 January 2019) Halogen-Free Status Low-Halogen For more information, please visit <u>Contact US</u> China ROHS Green Image ELV Not Relevant RoHS Phthalates Not Contained Search Parts in this Series 43045 Series Mates With Micro-Fit 3.0 Receptacle Housing 43025 // Micro-Fit 3.0 TPA Receptacle Housing 172952

Overview	use standard(s). <p> If it is determined during the</p>
Product Literature Order No	customer's evaluation of suitability, that higher
Product Name	performance is required, please contact Molex for
UPC	possible product options.""""""""""""""""""""""""""""""""""""
Physical Breakaway Circuits (Loaded) Circuits (maximum)	No 22 22
Color - Resin	Black
Durability (mating cycles max)	30
Flammability	94V-0
Glow-Wire Capable	Yes
Mated Height	17.64mm
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.895/g
Number of Rows	2
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	3.00mm
Plating min - Mating	0.381µm
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating Termination Interface: Style Electrical	-40° to +105°C Through Hole - Kinked Pin
Current - Maximum per Contact	8.5A
Voltage - Maximum	600V
Solder Process Data Duration at Max. Process Temperature (seconds) Lead-freeProcess Capability Max. Cycles at Max. Process Temperature Process Temperature max. C	030 SMC&WAVE 003 260
Material Info	
Reference - Drawing Numbers	PK-70873-0314-001
Packaging Specification	PS-43045, PS-43045-001, TS-43045-001-001,
Product Specification	TS-43045-002-001, TS-46235-001-001
Sales Drawing	SD-43045-005
Symbol/Footprint Data	SYM-43045-2212, SYM-43045-221X

This document was generated on 03/18/2019 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION