

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0705530112](#)
Status: **Active**
Overview: [SL Modular Connectors](#)
Description: 2.54mm Pitch SL Header, Low Profile, Single Row, Right Angle, 3.05mm Pocket, Shrouded, 8 Circuits, 0.76µm Gold (Au) Selective Plating, Tin (Sn) PC Tail Plating

Documents:

3D Model	Product Specification TS-70541-001-001 (PDF)
Drawing (PDF)	Product Specification TS-70541-100-001 (PDF)
Product Specification PS-70400-001 (PDF)	Packaging Specification PK-70873-0015 (PDF)
Product Specification PS-70541-001 (PDF)	RoHS Certificate of Compliance (PDF)



Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	70553
Application	Signal, Wire-to-Board
Overview	SL Modular Connectors
Product Name	SL
UPC	800754354615

Physical

Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Durability (mating cycles max)	50
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass, Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.105/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.30mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tube
Pitch - Mating Interface	2.54mm
Plating min - Mating	0.762µm
Plating min - Termination	1.905µm
Polarized to Mating Part	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	3.0A
-------------------------------	------

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[70553](#) Series

Mates With

SL Crimp Housing [70066](#) Option N, [70066](#)
Option G, [70430](#) Option G, [70400](#) Option G

Voltage - Maximum 250V

Solder Process Data

Duration at Max. Process Temperature (seconds) 003

Lead-free Process Capability WAVE

Max. Cycles at Max. Process Temperature 001

Process Temperature max. C 260

Material Info

Reference - Drawing Numbers

Packaging Specification PK-70873-0015

Product Specification PS-70400-001, PS-70541-001, TS-70541-001-001,

TS-70541-100-001

Sales Drawing SDA-70553-XXXX

This document was generated on 03/18/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION