

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0346750002

Status: Active

Overview: MX150 Sealed and Unsealed Connector System

Description: MX150 2 Way Inline Male Assembly with TPA, Single Row, 2 Circuits, Keying Option B, without Clip Slot, Gray



Series image - Reference only

Documents:

- 3D Model
- Drawing (PDF)
- Product Specification PS-34062-000-001 (PDF)
- Product Specification TS-34062-992-001 (PDF)
- Application Specification AS-34062-000-001 (PDF)
- Packaging Specification PK-31300-635-001 (PDF)
- RoHS Certificate of Compliance (PDF)

General

Product Family: Crimp Housings

Series: 34675

Application: Power, Wire-to-Board, Wire-to-Wire

Comments: without clip slot, without clip slot

More Detailed Tech Information: <http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications-Partnership>

Overview: MX150 Sealed and Unsealed Connector System

Product Name: MX150

UPC: 883906097776

Physical

Circuits (maximum): 2

Color - Resin: Gray

Gender: Plug

Glow-Wire Capable: No

Keying to Mating Part: Yes

Lock to Mating Part: Yes

Material - Resin: Nylon

Net Weight: 3.347/g

Number of Rows: 1

Packaging Type: Bag

Panel Mount: No

Pitch - Mating Interface: 5.00mm

Pitch - Termination Interface: 5.00mm

Polarized to Mating Part: Yes

Stackable: No

Temperature Range - Operating: -40° to +120°C

Solder Process Data

Lead-freeProcess Capability: N/A

Material Info

Reference - Drawing Numbers

Application Specification: AS-34062-000-001

Packaging Specification: PK-31300-635-001

Product Specification: PS-34062-000-001, TS-34062-992-001

Sales Drawing: SD-34675-001-000

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

34675 Series

Mates With

34062 MX150 Sealed Female Receptacles

Use With

34080 Male Terminal