

2000 Series

Built for **speed, accuracy and performance at an affordable price**, the robust 2000 series of hand-held digital thermometers provides a range of enhanced features to meet the changing demands of both **industrial and food environments**.

The rugged 2000 Series provides precise, **stable readings and high accuracy** even in the **harshest of environments**. They are **simple to operate, fast, reliable and built to last**. In this unique range we can offer advanced features such as dual input instruments which combined with interchangeable probe options makes this series a leader in its field. Optional coloured rubber boots add protection and style to these instruments.

General Specification

Resolution:	0.1° from -199.9°C to +199.9°C -199.9°F to +392.0°F 1°C elsewhere
Ambient Operating Temperature:	-10°C to +50°C/+14°F to +122°F (ambient)
Battery Type:	Two AA or equivalent cells (not supplied)
Battery Life:	Typically 500 hours
Low Battery Check:	Symbol appears on display
Display:	12.7mm / 0.5" custom L.C.D.
Sensor Open Circuit:	Indicated by 'O-C' on display
Overrange/Underrange:	'Out' displayed
Cold Junction Compensation:	Yes
Environmental Specifications:	IP65 (IP67 optional)
Auto Switch-Off Time:	12 minutes
Dimensions:	155 x 67 x 40mm/6.1 x 2.6 x 1.6"
Weight:	180g/6.4oz



2000T Model

For other options, please contact us digitronsales@rototherm.co.uk or +44 (0)1656 740551

Key Features and Benefits

- Long battery life – typically 500 hours
- Accurate performance – 0.2% of reading
- Robust Case – Ensuring long life in demanding and harsh environments
- Selectable auto switch-off – saves on operational costs
- Automatic zero calibration – for added accuracy

Optional Extras

- 2000BT – Protective Rubber Sleeve
- Carry Case
- Various Probe Options
- Calibration Certificate

Main Applications

A **world leader** in digital thermometers, Rototherm has become the standard for accurate and reliable measurement across the following industries:



Industrial



Food & Beverage

Model Specification

Model Options	2000T <i>(Refer to IEC 60584)</i>	2006T <i>(Refer to IEC 60584)</i>	2024T <i>(Refer to IEC 751)</i>	2029T <i>(Refer to IEC 60584)</i>
Sensor Type	K	T	Pt100	K T J N R S
Connector Type	2 pin mini	2 pin mini	TCM screw	2 pin mini
°C/°F Function*			•	•
Hold Function	•	•	•	•
Range Lock			•	•
Max/Min			•	•
Averaging			•	
Differential Input				•

Instrument Accuracies (All ± 1 Digit) <i>(Excluding probe error)</i>	2000T	0.1% rdg $\pm 0.2^{\circ}\text{C}/0.4^{\circ}\text{F}$ above $-100^{\circ}\text{C}/-148^{\circ}\text{F}$ 0.5% rdg $\pm 0.2^{\circ}\text{C}/0.4^{\circ}\text{F}$ below $-100^{\circ}\text{C}/-148^{\circ}\text{F}$
	2006T	$\pm 0.2^{\circ}\text{C}/0.4^{\circ}\text{F}$ over range -20°C to $+70^{\circ}\text{C}/-4^{\circ}\text{F}$ to $+158^{\circ}\text{F}$ $\pm 0.1\%$ rdg $\pm 0.2^{\circ}\text{C}/0.4^{\circ}\text{F}$ elsewhere
	2024T	$\pm 0.2\%$ rdg $\pm 0.1^{\circ}\text{C}/0.2^{\circ}\text{F}$ over range -150°C to $+800^{\circ}\text{C}/-238^{\circ}\text{F}$ to $+1472^{\circ}\text{F}$
	2029T	0.1% rdg $\pm 0.2^{\circ}\text{C}/0.4^{\circ}\text{F}$ above $-100^{\circ}\text{C}/-148^{\circ}\text{F}$ 0.5% rdg $\pm 0.2^{\circ}\text{C}/0.4^{\circ}\text{F}$ below $-100^{\circ}\text{C}/-148^{\circ}\text{F}$
Range	2000T	-200°C to $+1350^{\circ}\text{C}/-328^{\circ}\text{F}$ to $+2462^{\circ}\text{F}$
	2006T	-250°C to $+400^{\circ}\text{C}/-418^{\circ}\text{F}$ to $+752^{\circ}\text{F}$
	2024T	-150°C to $+800^{\circ}\text{C}/-238^{\circ}\text{F}$ to $+1472^{\circ}\text{F}$
	2029T K	-200°C to $+1350^{\circ}\text{C}/-328^{\circ}\text{F}$ to $+2462^{\circ}\text{F}$
	2029T T	-250°C to $+400^{\circ}\text{C}/-418^{\circ}\text{F}$ to $+752^{\circ}\text{F}$
	2029T J	-750°C to $+750^{\circ}\text{C}/-1318^{\circ}\text{F}$ to 1382°F
	2029T N	-200°C to $+1300^{\circ}\text{C}/-328^{\circ}\text{F}$ to $+2372^{\circ}\text{F}$
	2029T S	0°C to $+1750^{\circ}\text{C}/+32^{\circ}\text{F}$ to 3182°F

Technical Certification

- Certificate of Conformity
- Factory Test Certificate
- Factory Calibration Certificate

Export Documentation


- Certificate of Origin
- EUR1
- ATR

Calibration and After-Sales Support

- Fully trained field service personnel
- Use of UKAS certified calibration equipment
- 5 day turnaround
- Fixed pricing
- Approved manufacturer parts
- Full post-service reports
- 12 month warranty



ISO9001:2015
FM11958



For more information, please contact our service team
digitronservice@rototherm.co.uk