

This document was generated on 04/01/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: <u>0430450611</u>

Status: Active

Overview: Micro-Fit 3.0 Connector System Product Family

Description: Micro-Fit 3.0 Right-Angle Header, 3.00mm Pitch, Dual Row, 6 Circuits, with Solder Tab,

Gold, Glow-Wire Capable, Black

Documents:

Drawing (PDF)
3D Model
Product Specification

Product Specification PS-43045 (PDF)
Product Specification PS-43045-001 (PDF)
Product Specification TS-43045-001-001 (PDF)

Product Specification TS-43045-002-001 (PDF)

Product Specification TS-46235-001-001 (PDF)
Packaging Specification 430450001-PK-000 (PDF)
Packaging Specification PK-70873-05XX-001 (PDF)

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

Agency Certification

CSA UL

General

Product Family Series

Application Comments LR19980 E29179

PCB Headers

<u>43045</u>

Power, Wire-to-Board

"""""High Temperature|Square Pin|Solder Type<P><P>This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product enduse standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options."""""", """"""High Temperaturel

Square Pin|Solder Type<P><P>This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-



EU ELV

Not Relevant

EU RoHS Compliant

REACH SVHC

Not Contained Per -ED/88/2018 (15 January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit Contact US

China RoHS

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series

43045 Series

Mates With

Micro-Fit 3.0 Receptacle Housing <u>43025</u>

- Since the description of the second seco use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for

possible product options.""""""

Overview <u>Micro-Fit 3.0 Connector System Product Family</u>

Product Literature Order No 987650-5984
Product Name Micro-Fit 3.0
UPC 800754371162

Physical

Breakaway No Circuits (Loaded) 6 Circuits (maximum) 6 Color - Resin Black Durability (mating cycles max) 30 Flammability 94V-0 Glow-Wire Capable Yes Mated Height 10.29mm Material - Metal **Brass** Material - Plating Mating Gold Material - Plating Termination

Material - Resin High Temperature Thermoplastic

Net Weight 1.124/g Number of Rows 2

Orientation Right Angle
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.60mm

Packaging Type Embossed Tape on Reel

Pitch - Mating Interface 3.00mm
Plating min - Mating 0.762µm
Polarized to PCB Yes
Shrouded Fully
Stackable No
Surface Mount Compatible (SMC) N/A

Temperature Range - Operating -40° to +105°C
Termination Interface: Style Surface Mount

Electrical

Current - Maximum per Contact 8.5A Voltage - Maximum 600V

Solder Process Data

Duration at Max. Process Temperature (seconds)

Lead-freeProcess Capability

Max. Cycles at Max. Process Temperature

003

Process Temperature max. C

260

Material Info

Reference - Drawing Numbers

 Packaging Specification
 430450001-PK-000, PK-70873-05XX-001

 Product Specification
 PS-43045, PS-43045-001, TS-43045-001-001,

TS-43045-002-001, TS-46235-001-001

Sales Drawing SD-43045-004-000

This document was generated on 04/01/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION