



### Main

Device short name	9001SK
-------------------	--------

### Complementary

Bezel material	Black plastic
Shape of signaling unit head	Round
Operator position information	2 positions
Mechanical durability	5000000 cycles
Device presentation	Basic element

### Environment

protective treatment	TC
ambient air temperature for storage	-40...70 °C
ambient air temperature for operation	-25...70 °C
overvoltage category	Class II conforming to IEC 61140
IP degree of protection	IP66
NEMA degree of protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 4X
product certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03
vibration resistance	7 gn (f = 2...500 Hz) conforming to IEC 60068-2-6

### Offer Sustainability

Sustainable offer status	785901039716
RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.