

This document was generated on 04/01/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0430451214

Status: **Active**

Micro-Fit 3.0 Connector System Product Family Overview:

Description: Micro-Fit 3.0 Vertical Header, 3.00mm Pitch, Dual Row, 12 Circuits, with PCB

Polarizing Peg, Gold, Glow-Wire Capable, Black

Documents:

3D Model Product Specification TS-43045-002-001 (PDF) Drawing (PDF) Product Specification TS-46235-001-001 (PDF) Packaging Specification PK-70873-0314-001 (PDF) Product Specification PS-43045 (PDF) Product Specification PS-43045-001 (PDF) RoHS Certificate of Compliance (PDF)

Product Specification TS-43045-001-001 (PDF) Product Literature (PDF)

Agency Certification

CSA UL

General

Product Family Series Application Comments


LR19980 E29179

PCB Headers

43045

Power, Wire-to-Board

"""""High Temperature|Square Pin|Offset Through Hole Mounting|Solder Type<P><P>This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options."""""", """"""High Temperaturel Square Pin|Offset Through Hole Mounting|Solder Type<P><P>This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-



EU ELV

Not Relevant

EU RoHS Compliant

REACH SVHC

Not Contained Per -ED/88/2018 (15 January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit Contact US

China RoHS

China ROHS Green Image **ELV** Not Relevant **RoHS Phthalates** Not Contained

Search Parts in this Series

43045 Series

Mates With

Micro-Fit 3.0 Receptacle Housing 43025
-kir>Micro-Fit 3.0 TPA Receptacle Housing 172952

use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for

possible product options.""""""

Overview Micro-Fit 3.0 Connector System Product Family

Product Literature Order No 987650-5984
Product Name Micro-Fit 3.0
UPC 800754373166

Physical

Breakaway No Circuits (Loaded) 12 Circuits (maximum) 12 Color - Resin Black Durability (mating cycles max) 30 Flammability 94V-0 Glow-Wire Capable Yes Mated Height 17.64mm Material - Metal **Brass** Material - Plating Mating Gold Material - Plating Termination

Material - Resin High Temperature Thermoplastic

Net Weight 1.686/g Number of Rows Orientation Vertical **PCB** Locator Yes **PCB** Retention Yes PCB Thickness - Recommended 1.60mm Packaging Type Tray Pitch - Mating Interface 3.00mm Plating min - Mating 0.762um Polarized to PCB Yes Shrouded **Fully** Stackable No Surface Mount Compatible (SMC)

Temperature Range - Operating -40° to +105°C

Termination Interface: Style Through Hole - Kinked Pin

Electrical

Current - Maximum per Contact 8.5A Voltage - Maximum 600V

Solder Process Data

Duration at Max. Process Temperature (seconds) 030

Lead-freeProcess Capability SMC&WAVE

Max. Cycles at Max. Process Temperature 003
Process Temperature max. C 260

Material Info

Reference - Drawing Numbers

Packaging Specification PK-70873-0314-001

Product Specification PS-43045, PS-43045-001, TS-43045-001,

TS-43045-002-001, TS-46235-001-001

Sales Drawing SD-43045-005

Symbol/Footprint Data SYM-43045-1212, SYM-43045-121X

This document was generated on 04/01/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION