


	CPC
PRODUCT NO.	CS32771



- (1). Cable Spec: 28AWG (7/0.127TC)*1PR+24AWG (7/0.2TC)*2C+AL+D(1/0.254BC)+B(64/0.12LMS)
 Jacket Material: PVC OD: 4.8mm
 Colour: Black
 Cable Printing: AWM STYLE 2725 80°C 30V VW-1 USB 2.0 High Speed Cable-RoHS
- (2). Connector A: USB2.0 B Female Solder Type
 Insulation: White
 Contact: Gold Plated
 Shell: Fe, Nickel Plated
- (3). Connector B: USB B Male Solder Type
 Insulation: White
 Contact: Gold Plated
 Shell: Fe, Nickel Plated
- (4). MOLDED: LD-PE
- (5). MOLDED: 45P PVC-BLACK
- (6). THUMB SCREW: NUT-NICKEL PLATED (#4-40)
- (7). CROSS SCREW: Nickel Plated (#4-40*15)
- (8). ELECTRONIC TEST:
 A. OPEN/SHORT/INTERMITTENCE: 100%.
 B. HI-POT: AC 300V 0.01S
 C. INSULATION RESISTANCE: DC300V 0.01S 10MΩ (MIN)
 D. CONDUCTIVE RESISTANCE: 5 OHM (MAX)

PIN OUT: (8)

SIDE:A	SIDE:B
USB2.0 BF	USB2.0 BM
1	1 RED
2	2 WHITE
3	3 GREEN
4	4 BLACK
SHELL	SHELL

GENERAL TOLERANCES (UNLESS SPECIFIED)					
LENGTH: X. ±1 .X±0.2 .XX±0.10		UNIT: mm	REV: 00		
ANGLE: X° . ±1° .X° ±0° 30'		DRAWING	GDG	2019/03/29	S. P. NO.
		CHECK			P. O. NO.
		APPROVE			NAME
					USB2.0 BM-BF
00	NEW	2019/03/29			
REV	DESCRIPTION	DATE			
				SIZE	PAGE
					1/1

00	NEW	2019/03/29
REV	DESCRIPTION	DATE