LQH55DN151M03# "#" indicates a package specification code.












< List of part numbers with package codes > LQH55DN151M03L , LQH55DN151M03K

Shape





Notes

When rated current is applied to the products, inductance will be within ±40% of initial inductance value.

When rated current is applied to the products, the temperature rise caused by self-generated heat shall be limited to 40 $^{\circ}\text{C}$ max.

References

Packaging code	Specifications	Minimum quantity
L	φ180mm Embossed taping	350
К	φ330mm Embossed taping	1500

	Mass (Typ.)	
1 piece		0.48g

Specifications

Inductance	150μH ±20%
Inductance test frequency	100kHz
Rated current (Itemp) (Based on Temperature rise)	0.42A
Max. of DC resistance	2.66Ω
Avg. of DC resistance	1.9Ω±40%
Self resonance frequency (min.)	5.0MHz
Operating temperature range (Self-temperature rise is not included)	-40°C to 80°C
Class of magnetic shield	No Shield
Series	LQH55DN_03

1 of 2



^{1.} This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.




^{2.} This datasheet has only typical specifications because there is no space for detailed specifications

Chart of characteristic data (The charts below may show another part number which shares its characteristics.)

Inductance-Current characteristics (Typ.)



Impedance-Frequency characteristics (Typ.)



2 of 2



1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

