

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0768710006](#)  
**Status:** **Active**  
**Overview:** [QSFP+ Interconnect Solution](#)  
**Description:** Quad Small Form-factor Pluggable Plus (QSFP) Assembly, Stacked 2 by 1 with Elastomer Gaskets and Light Pipes, Tin

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-76870-001-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification AS-76871-0002-001 (PDF)</a>
<a href="#">Product Specification PS-76870-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

UL E29179


**General**

Product Family	I/O Connectors
Series	<a href="#">76871</a>
Application	Module-to-Board
Component Type	Receptacle
Electrical Model	Yes
Overview	<a href="#">QSFP+ Interconnect Solution</a>
Product Name	QSFP
Type	N/A
UPC	884982637214

**Physical**

Boot Color	N/A
Circuits (Loaded)	76
Circuits (maximum)	76
Durability (mating cycles max)	100
Flammability	94V-0
Gender	Female
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	40.208/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	1.25mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	2
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Through Hole - Compliant Pin
Waterproof / Dustproof	No

**Electrical**



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/61/2018 (27 June 2018)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[76871](#) Series

**Use With**

[74757](#) , [74758](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

<b>Description</b>	<b>Product #</b>
--------------------	------------------

QSFP+ and zQSFP+	<a href="#">622025300</a>
------------------	---------------------------

Multi-Port Connector	
----------------------	--

Tooling	
---------	--

Multi-Port Connector	<a href="#">622030390</a>
----------------------	---------------------------

Extraction Tool	
-----------------	--

Current - Maximum per Contact	0.5A
Grounding to Panel	None
Shield Type	EMI Gasket
Shielded	Yes
Voltage - Maximum	120V AC (RMS)/DC

**Solder Process Data**

Lead-free Process Capability	N/A
------------------------------	-----

**Material Info****Reference - Drawing Numbers**

Application Specification	AS-76870-001-001, AS-76871-0002-001
Electrical Model Document	EE-76870-001
Product Specification	PS-76870-001-001
S-Parameter Model	SP-76870-001
Sales Drawing	SD-76871-001

This document was generated on 04/01/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**